



24W

VT-2407 24W LED PREMIUM PANEL COLORCODE:6400K ROUND

Lumens 2000	Beam Angle 120	Dimensions Ø300x12mm
-----------------------	--------------------------	--------------------------------

White
 SKU:4874



Technical Information

Instant Start: 0-100% in 1/1s	LED Chip Type: SMD
Watts: 24	IP Rating: IP20
Lumens: 2000	Dimmable: No
Shape: Round	Warranty (Years): 2
Beam Angle: 120	PF: >0.7
Cutting Size: 280mm	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium	Input Power: AC:85-265V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 24H*

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.9
Length(Box)mm	375
Width(Box)mm	300
Height(Box)mm	35
Unit CBM	0.0041323

Listing Details

EAN Code	3800157601573
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	360

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES