



**45W**  
45W DIMMABLE DRIVER FOR PANEL

SKU:6019

**2** YEARS  
WARRANTY

## Technical Information

Watts: 45

Body Type: ABS Plastic

IP Rating: IP20

Dimmable: Yes

Warranty (Years): 2

Operation Temperature: -25 to +50°C

## Features

- ✓ Easy to Install
- ✓ Suitable with V-TAC Panels(Fixture Not Included)
- ✓ Application - Office, Conference Room, Schools, Lobby, Cabin, Kitchen etc

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.21
Length(Box)mm	185
Width(Box)mm	15
Height(Box)mm	65
Unit CBM	0.000408

## Listing Details

EAN Code	3800157604017
Commodity Code	8504409090

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
---------------------------------	----

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES