



36W

VT-6237 36W LED PANEL 600x600 COLORCODE:3000K

Lumens 3240	Beam Angle 120	Dimensions 595x595mm
-----------------------	--------------------------	--------------------------------

Warm White
SKU:8083

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Output Voltage:	DC:30-42V	LED Chip Type:	SMD
Watts:	36	IP Rating:	IP20
Lumens:	3240	Dimmable:	No
Shape:	Square	Warranty (Years):	2
On/Off Cycles:	>10000	PF:	>0.9
Beam Angle:	120	CRI:	>80
Output Current:	860mA	Operation Temperature:	-20°C to +40°C
Unit Color:	White	Input Power:	AC:220-240V,50/60Hz
Body Type:	Aluminium + PS + PP	Sensor Compatibility:	Yes
Long life:	20,000 Hours		

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.918333
Unit CBM	0.01044

Listing Details

EAN Code	3800157646925
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
---------------------------------	---

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES