

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2065230242](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Receptacle, Dual Row, UL94-HB, without CPA, 24 Circuits, Polarization Option B, Gray

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-31301-538-001 \(PDF\)](#)
[Product Specification 2065230000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 2065230000-AS-000 \(PDF\)](#)

General

Product Family Crimp Housings
Series [206523](#)
Application Automotive, Power, Wire-to-Board
Overview [Mini50 Connection Systems](#)
Polarization B
Product Name Mini50
UPC 191128857093


Physical

Circuits (maximum) 24
Color - Resin Gray
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin PBT
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 2.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +100°C

Material Info

Reference - Drawing Numbers

Application Specification 2065230000-AS-000
Packaging Specification PK-31301-538-001
Product Specification 2065230000-PS-000
Sales Drawing 2065230000-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[206523](#) Series

Mates With

Mini50 Surface Mount Header [348978241](#), [348979241](#)
 Mini50 Vertical Through-Hole Header [348250241](#), [348259241](#)
 Mini50 Right-Angle Through-Hole Header [348260241](#), [348269241](#)

Use With

CTX50 Unsealed Terminals [560023](#)