


DPB22-K11R

Mushroom head with key push button 1a 1b red



SPECIFICATION

Button Head Material	PA66 V2
Body Material	PA66 + 15% GF-VO
Locknut Material	PA66 V2 +15%GF
Button Head Lamp Colour	Red
Number of Contact Blocks	2
Shaft Style	Standard
Max Wire Size Single Strand (Sq mm)	2.5
Max Wire Size Multi Strand (Sq mm)	1.5
Min Temperature Rating °C	-10
Max Temperature Rating °C	65
Panel Hole Size	22.5mm
IP Rating	56
Key Material	Brass, Nickel Plated
Product Sub Type	Mushroom head with key
Product Type	Push button non-illuminated
Terminal Type	Screw clamp