

## Interface module - FLKM 20/KDS3-MT/SC053 - 2906440


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE termination board with knife disconnection and 20-pos. flat cable connector, module width: 111 mm



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 055626 076614
GTIN	4055626076614
Weight per Piece (excluding packing)	225.000 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	111 mm
Height	77 mm
Depth	60 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Maximum altitude	< 2000 m
Degree of protection	IP00
	≥ IP54 (Installation location)

#### General

Nominal voltage $U_N$	< 50 V DC
	< 25 V AC
Max. perm. current (per branch)	1 A

# Interface module - FLKM 20/KDS3-MT/SC053 - 2906440

## Technical data

### General

Mounting position	any
-------------------	-----

### Connection data

Connection name	Field level
Connection method	Screw connection with disconnect knife
Screw thread	M3
Number of positions	20
Conductor cross section solid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	24 ... 12

### Connection data 2

Connection name	Controller level
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	20
Pitch	2.54 mm

### Standards and Regulations

Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178: 1998-04
Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 µs)
Insulation	Functional insulation
Pollution degree	2
Overvoltage category	II

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Classifications

#### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

## Interface module - FLKM 20/KDS3-MT/SC053 - 2906440

### Classifications

#### ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780
ETIM 7.0	EC002780

#### UNSPSC

UNSPSC 13.2	39121432
UNSPSC 18.0	39121432
UNSPSC 19.0	39121432
UNSPSC 20.0	39121432
UNSPSC 21.0	39121432