


KEMET, MPXV, Power, 330 nH, 20%



Dimensions

Dimensions	
L	5.3mm +/-0.2mm
W	5mm +/-0.2mm
T	2mm MAX
LL	1mm NOM
G	2.5mm +/-0.2mm

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	3500

General Information

Series:	MPXV
Style:	SMD
Description:	Surface Mount Inductor
Features:	Power Inductors
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Core:	Composite
Miscellaneous:	40 (K) Temperature Rise Max.

Specifications

Inductance:	0.33 uH (100 KHz)
Inductance Tolerance:	20%
Temperature Range:	-55/+155°C
Shielded:	Yes
Current:	13.4 A (Irms, 40C Rise By Self Heating), 11 A (Isat, 20% Drop In Inductance), 16 A (Isat, 30% Drop In Inductance)
DC Resistance:	6.2 mOhms
Self-Resonant Frequency:	110 MHz