



**40W**

VT-6140 40W LED PANEL 595\*595MM COLORCODE:4000K SQUARE

Lumens <b>4400</b>	Beam Angle <b>120</b>	Dimensions <b>595x595x12mm</b>
-----------------------	--------------------------	-----------------------------------

Day White  
SKU:6331

**5 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP65
Watts: 40	Dimmable: No
Lumens: 4400	Warranty (Years): 5
On/Off Cycles: >20000	PF: >0.9
Beam Angle: 120	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium + PS	Input Power: DC:25-42V
Long life: 30,000 Hours	Sensor Compatibility: Yes
LED Chip Type: SMD	

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours

## Packaging

### Unit Details

Gross Weight(GW) Kgs	3.615
Length(Box)mm	620
Width(Box)mm	40
Height(Box)mm	660
Unit CBM	0.016104

### Listing Details

EAN Code	3800157620093
Commodity Code	9405403990



### Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
Qty Per Pallet	90

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES