



10W

VT-820 10W LED WALL LIGHT COLORCODE:3000K GREY BODY 80CM HEIGHT

Lumens <b>450</b>	Beam Angle <b>72</b>	Dimensions <b>108x800mm</b>
----------------------	-------------------------	--------------------------------

Warm White  
 SKU:8328




### Technical Information

Watts:	10	Dimmable:	No
Lumens:	450	Warranty (Years):	2
Beam Angle:	72	PF:	>0.5
Unit Color:	Grey	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	COB(CREE)	Sensor Compatibility:	Yes
IP Rating:	IP65		

### Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	2.4
Unit CBM	0.027864

## Listing Details

EAN Code	3800157632393
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	60

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES