



10W

VT-820 10W LED WALL LIGHT COLORCODE:3000K BLACK BODY 80CM HEIGHT

Lumens 450	Beam Angle 72	Dimensions 108x800mm
----------------------	-------------------------	--------------------------------

Warm White
 SKU:8331




Technical Information

Watts:	10	Dimmable:	No
Lumens:	450	Warranty (Years):	2
Beam Angle:	72	PF:	>0.5
Unit Color:	Black	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	COB(CREE)	Sensor Compatibility:	Yes
IP Rating:	IP65		

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.4
Unit CBM	0.027864

Listing Details

EAN Code	3800157632423
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	60

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES