



12W

VT-822 12W LED WALL LIGHT COLORCODE:3000K WHITE BODY

Lumens <b>750</b>	Beam Angle <b>140</b>	Dimensions <b>130x160mm</b>
----------------------	--------------------------	--------------------------------

Warm White  
 SKU:8334

**2** YEARS  
 WARRANTY



## Technical Information

Watts:	12	IP Rating:	IP65
Lumens:	750	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	140	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	PC	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz

## Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.487
Unit CBM	0.002618

### Listing Details

EAN Code	3800157632454
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	400

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES