



12W

VT-822 12W LED WALL LIGHT COLORCODE:3000K BLACK BODY

Lumens 750	Beam Angle 140	Dimensions 130x160mm
----------------------	--------------------------	--------------------------------

Warm White
 SKU:8340

2 YEARS
 WARRANTY



Technical Information

Watts: 12	Dimmable: No
Lumens: 750	Warranty (Years): 2
Beam Angle: 140	PF: >0.5
Unit Color: Black	CRI: >80
Body Type: PC	Operation Temperature: -20 to +45°C
Long life: 20,000 Hours	Input Power: AC:100-240V,50/60Hz
IP Rating: IP65	

Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

Packaging

Unit Details

Gross Weight(GW) Kgs 0.482

Unit CBM 0.002856

Listing Details

EAN Code 3800157632515

Commodity Code 9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton) 20

Qty Per Pallet 400

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES