



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	07/24/19	MMARTINEZ

NB14-18-FRK-10F CONTAINS:

- 4 #6 U-TYPE SPEED NUT
- 4 #6 2.0 STAINLESS STEEL PAN HEAD PHILLIPS SHEET METAL SCREW
- 1 120X120mm ALUMINUM MESH FILTER
- 1 120x120x38mm 120VAC COOLING FAN 16.4W

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [.51] .XXX = .005 [.13]	APPROVALS DRAWN BY DZINN	DATE 07/24/2019	 50 HIGH STREET NORTH ANDOVER, MA 01845
	CHECKED BY MMARTINEZ	DATE 07/24/2019	
PROJECTION 	APPROVED BY MMARTINEZ	DATE 07/24/2019	PRODUCT DESCRIPTION FAN REPL KIT-14/18" ENCL 120VAC
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A
FSCM NO. 43321		DWG. NO. NB14-18-FRK-10F	REV. A
SCALE: NONE		CAD FILE: NB14-18-FRK-10F.SLDDRW	SHEET 1 OF 1