



4W

VT-2145D 4W ST64 FILAMENT BULB-AMBER GLASS COLORCODE:2200K
 B22 Dimmable

Equivalent 30W	Lumens 350	Beam Angle 300	Dimensions 64x138mm
--------------------------	----------------------	--------------------------	-------------------------------

Warm White
 SKU:7420



Technical Information

EQ-WATTS: 30	Long life: 30,000 Hours
Watts: 4	LED Chip Type: Filament
Lumens: 350	IP Rating: IP20
Holder Type: B22	Dimmable: Yes
Shape: ST64	Warranty (Years): 2
On/Off Cycles: >15000	PF: >0.5
Beam Angle: 300	CRI: >80
Unit Color: Amber	Operation Temperature: -20 to +45°C
Body Type: Glass	Input Power: AC:220-240V,50Hz
Energy Rating: A+	



Features

- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ Stable LED Filament technology for extended lifespan
- ✓ Glass body available in Clear, Frost and Amber Shades
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ Crafted with Splendid filament designs
- ✓ Multiple Configurations for enriched antique vintage ambiance
- ✓ Excellent Heat Radiation Efficiency
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Dimmable & Non Dimmable options
- ✓ Broad Range of holders (E27, E14, B22) & Shapes (Candle, Globe, A60, Candle Flame, ST64, T30)
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.0726
Unit CBM	0.000684

Listing Details

EAN Code	3800157633086
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	100
---------------------------------	-----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES