

COLEMAN CABLE

Outdoor Extension Cords
Cool Colors™

Contractor Grade SJTW cord features a neon jacket in a variety of colors for added safety and theft deterrence on the jobsite. Features clear molded plugs with power indicator light in female end receptacle to show that the power is on. Added features include heavy duty strain relief and reinforced blades and ground pin.

Wire Type: SJTW
125V Rating: 15A



Mfg Part#	Wire	Color	Length	Master Pk Qty	Master Pk Wt
02577-88-0A	12/3	Neon Pink	25	12	40
02577-88-0H	12/3	Neon Blue	25	12	40
02577-88-0Q	12/3	Neon Purple	25	12	40
02577-88-0X	12/3	Neon Green	25	12	40
02577-88-04	12/3	Neon Red	25	12	40
02578-88-0A	12/3	Neon Pink	50	8	53
02578-88-0H	12/3	Neon Blue	50	8	53
02578-88-0Q	12/3	Neon Purple	50	8	53
02578-88-0X	12/3	Neon Green	50	8	53
02578-88-04	12/3	Neon Red	50	8	53
02578-88-03	12/3	Neon Orange	50	8	53
02579-88-0A	12/3	Neon Pink	100	4	52
02579-88-0H	12/3	Neon Blue	100	4	52
02579-88-0Q	12/3	Neon Purple	100	4	52
02579-88-0X	12/3	Neon Green	100	4	52
02579-88-04	12/3	Neon Red	100	4	52
02579-88-03	12/3	Neon Orange	100	4	52
<i>Tri-Source Three-Way Power Block</i>					
04178-88-0H	12/3	Neon Blue	50	6	42
04178-88-04	12/3	Neon Red	50	6	42
04178-88-03	12/3	Neon Orange	50	6	42
04179-88-0H	12/3	Neon Blue	100	4	53
04179-88-04	12/3	Neon Red	100	4	53
04179-88-03	12/3	Neon Orange	100	4	53

COLEMAN CABLE

High Visibility/Low Temperature Extension Cords
All-Weather Cords with Lighted End

High visibility, bright blue cord is easily identified on the jobsite. Coleman Cable's new vinyl compound provides super-flexibility at temperatures down to -45°F. Reinforced blades help prevent accidental bending or breaking and a heavy-duty strain relief protects electrical connections resulting in longer cord life. High Visibility/Low Temperature extension cords come standard with power indicator light in the female receptacle to show that the power is on.



Mfg Part#	Wire	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
02367	16/3	SJTW	Hi-Vis Blue	25	13A	12	19
02368	16/3	SJTW	Hi-Vis Blue	50	13A	12	38
02369	16/3	SJTW	Hi-Vis Blue	100	10A	6	35
02467	14/3	SJTW	Hi-Vis Blue	25	15A	6	13
02468	14/3	SJTW	Hi-Vis Blue	50	15A	6	26
02469	14/3	SJTW	Hi-Vis Blue	100	13A	3	34
02568	12/3	SJTW	Hi-Vis Blue	50	15A	4	24
02569	12/3	SJTW	Hi-Vis Blue	100	15A	4	24
<i>Tri-Source® Three-Way Power Block</i>							
03267	14/3	SJTW	Hi-Vis Blue	25	15A	6	14
03268	14/3	SJTW	Hi-Vis Blue	50	15A	6	27
04168	12/3	SJTW	Hi-Vis Blue	50	15A	6	40
04169	12/3	SJTW	Hi-Vis Blue	100	15A	4	51

COLEMAN CABLE

Outdoor Extension Cords

Insulated with Power Indicator Light

Polar/Solar Plus™

America's premier extension cord, Polar/Solar Plus™ is lightweight and stays flexible to -67°F. Its rugged T*Prene® insulation provides superior resistance to abrasion, ozone, oil, grease, and chemicals. Plus, the outer jacket is flame retardant and water resistant. Polar/Solar Plus™ Extension Cords feature a power indicator light in the female receptacle to show that the power is on.

Note: 01788, 01789 - Cap and Connector rated 15A

Wire Type: SJEOW

Color: Yellow



Mfg Part#	Wire	Length	125V	Master Pk Qty	Master Pk Wt
01287	16/3	25	13A	12	19
01288	16/3	50	13A	12	38
01289	16/3	100	10A	6	35
01487	14/3	25	15A	12	27
01488	14/3	50	15A	6	26
01489	14/3	100	13A	6	49
01687	12/3	25	15A	12	39
01688	12/3	50	15A	6	38
01689	12/3	100	15A	4	48
01788	10/3	50	15A	4	42
01789	10/3	100	15A	3	63

COLEMAN CABLE

Outdoor Extension Cords - Tri-Source®

3-Way Power Block with Insulation and Power Indicator Light

Polar/Solar Plus™

America's premier extension cord, Polar/Solar Plus™ is lightweight and stays flexible to -67°F. Its rugged T*Prene® insulation provides superior resistance to abrasion, ozone, oil, grease, and chemicals. Plus, the outer jacket is flame retardant and water resistant. Polar/Solar Plus™ Extension Cords feature a power indicator light in the female receptacle to show that the power is on.

Color: Yellow



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
03412**	12/3	SEOW	2	15A	12	10
03482	12/3	SEOW	2	15A	12	10
03487	12/3	SJEOW	25	15A	12	42
03488	12/3	SJEOW	50	15A	6	39
03489	12/3	SJEOW	100	15A	4	49
03588***	10/3	SJEOW	50	15A	4	43
03589***	10/3	SJEOW	100	15A	3	62

*Cap and Connector rated 15A

**Does not have a Power Indicator Light

***Not UL, CSA Listed

COLEMAN CABLE

Outdoor Extension Cords - Quadnector®

4-Way Power Block with Insulation and Power Indicator Light

Polar/Solar Plus™

America's premier extension cord, Polar/Solar Plus™ is lightweight and stays flexible to -67°F. Its rugged T*Prene® insulation provides superior resistance to abrasion, ozone, oil, grease, and chemicals. Plus, the outer jacket is flame retardant and water resistant. Polar/Solar Plus™ Extension Cords feature a power indicator light in the female receptacle to show that the power is on.

Color: Yellow



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
04422	12/3	SJEOW	6	15A	6	9
04427	12/3	SJEOW	25	15A	6	24
04428	12/3	SJEOW	50	15A	4	30
04429	12/3	SJEOW	100	15A	4	53
<i>600 Volt Rated</i>						
04522	12/3	SEOW	6	15A	6	11
04527	12/3	SEOW	25	15A	6	34

COLEMAN CABLE

Outdoor Extension Cords

Insulation and Power Indicator Light

Polar/Solar Plus™ Extra-Hard Service

America's premier extension cord, Polar/Solar Plus™ is lightweight and stays flexible to -67°F. Its rugged T*Prene® insulation provides superior resistance to abrasion, ozone, oil, grease, and chemicals. Plus, the outer jacket is flame retardant and water resistant. Polar/Solar Plus™ Extension Cords feature a power indicator light in the female receptacle to show that the power is on.

Color: Yellow



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
01567	14/3	SEOW	25	15A	6	24
01568	14/3	SEOW	50	15A	4	32
01569	14/3	SEOW	100	15A	3	46
01767	12/3	SEOW	25	15A	6	31
01768	12/3	SEOW	50	15A	4	39
01769	12/3	SEOW	100	15A	3	57

COLEMAN CABLE

Outdoor Extension Cords

Polar/Solar™ Coiled Cords

Tangle-free self-coiling cord never needs winding coil, and offers coiled cord flexibility with Polar/Solar® cord toughness. Molded right angle plug helps prevent accidental disconnection.



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
01220	16/3	SJEOW	1-5	13A	6	6
01226	16/3	SJEOW	4-20	13A	12	12

COLEMAN CABLE

Outdoor Extension Cords

Polar/Solar™ Coiled Cords

Tangle-free self-coiling cord never needs winding coil, and offers coiled cord flexibility with Polar/Solar® cord toughness. All cords listed below do not include molded ends.



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
09809	18/2	SJEOW	4-20	-	10	14
09810	18/3	SJEOW	4-20	-	12	21
09811	18/4	SJEOW	4-20	-	10	19
09812	16/2	SJEOW	4-20	-	10	17
09813	16/3	SJEOW	4-20	-	10	21
09814	16/4	SJEOW	4-20	-	10	25
09815	14/3	SEOW	4-20	-	5	29
09816	12/3	SEOW	4-20	-	5	37

COLEMAN CABLE

Push-Lock® Extension Cords

Locking Extension Cords

These cords use a patented Push-Lock® mechanism which stays connected until you want the cords disengaged. These are ideal for lawn and power tool applications. They have a lighted connector to indicate power is "on".



Mfg Part#	Wire	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
02418-88-26	14/3	SJTW	Yellow/Blue	45	15A	4	21
02419-88-26	14/3	SJTW	Yellow/Blue	90	15A	3	29
02518-88-28	12/3	SJTW	Yellow/Blue	45	15A	4	27
02519-88-28	12/3	SJTW	Yellow/Blue	90	15A	3	40

COLEMAN CABLE

Outdoor Extension Cords

Stripes™

Increase safety awareness and help to prevent job-site loss or theft with neon STRIPES™ outdoor extension cords. Each extension cord features a dominant color and a colored stripe that runs the length of the cord. All STRIPES™ extension cords have a power indicator light in the female end receptacle to show that the power is on.

Wire Type: SJTW
125V Rating: 15A



Mfg Part#	Wire	Color	Length	Master Pk Qty	Master Pk Wt
02548-88-54	12/3	Lime Green/Red	50	8	53
02548-88-22	12/3	Yellow Purple	50	8	53
02548-88-52	12/3	Dark Green/ Yellow	50	8	53
02548-88-64	12/3	Blue/Red	50	8	53
02548-88-41	12/3	Red/White	50	8	53
02548-88-77	12/3	Pink/Lime Green	50	8	53
02548-88-NV	12/3	Silver/Blue	50	8	53
02548-88-3V	12/3	Orange/Blue	50	8	53
02548-88-P1	12/3	Purple/White	50	8	53
02508-06-41	12/3	Red/White/Blue	50	8	53
02549-88-54	12/3	Lime Green/Red	100	4	52
02549-88-22	12/3	Yellow/Purple	100	4	52
02549-88-52	12/3	Dark Green/ Yellow	100	4	52
02549-88-64	12/3	Blue/Red	100	4	52
02549-88-41	12/3	Red/White	100	4	52
02546-88-77	12/3	Pink/Lime Green	100	4	52
02549-88-NV	12/3	Silver/Blue	100	4	52
02549-88-3V	12/3	Orange/Blue	100	4	52
02549-88-P1	12/3	Purple/White	100	4	52
02509-06-41	12/3	Red/White/Blue	100	6	52
02648-00-54	10/3	Lime Green/Red	50	4	46
02648-00-64	10/3	Blue/Red	50	4	46
02649-00-54	10/3	Lime Green/Red	100	3	68
02649-00-64	10/3	Blue/Red	100	3	68

COLEMAN CABLE

Multi-Outlet Vinyl Extension Cords 3 and 4-Way Power Blocks

Innovative blocks provide additional outlets for power distribution. Vinyl jacket resists moisture, abrasion, and prolonged exposure to sunlight. Reinforced blades help prevent accidental bending or breaking and heavy-duty strain relief protects electrical connections resulting in longer cord life.



Mfg Part#	Wire	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
Tri-Source® 3-Way Power Block							
04003*	16/3	SJTW	Orange	3	13A	24	26
04006*	16/3	SJTW	Orange	9	13A	24	35
04004	14/3	SJTW	Orange	6	15A	18	19
04217	14/3	SJTW	Red	25	15A	12	33
04218	14/3	SJTW	Red	50	15A	6	30
04219	14/3	SJTW	Red	100	13A	6	55
Tri-Source® 3-Way Power Block with Lighted End							
04112	12/3	STW	Yellow	2	15A	12	11
04187	12/3	SJTW	Yellow	25	15A	12	45
04188	12/3	SJTW	Yellow	50	15A	6	42
04189	12/3	SJTW	Yellow	100	15A	4	53
Quadnector® 4-Way Power Block							
04102*	12/3	SJTW	Orange	6	15A	6	9
04107*	12/3	SJTW	Orange	25	15A	6	25
04108*	12/3	SJTW	Orange	50	15A	4	32
04109*	12/3	SJTW	Orange	100	15A	4	56
Quadnector® 4-Way Power Block - 600 Volt Rated							
04207*	12/3	STW	Orange	25	15A	6	36
04208*	12/3	STW	Orange	50	15A	4	47
04209*	12/3	STW	Orange	100	15A	3	67
<i>*Rated for Indoor Use Only</i>							

COLEMAN CABLE

Vinyl Outdoor Extension Cords

These all-purpose cords resist moisture, abrasion, and prolonged exposure to sunlight for durability. Molded, water resistant connectors with reinforced blades make these cords suitable for outdoor use.



Mfg Part#	Wire	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
Two Conductor							
02204	16/2	SJTW	Orange	10	13A	24	18
02210	16/2	SJTW	Black	15	13A	24	19
02207	16/2	SJTW	Orange	25	13A	12	16
02208	16/2	SJTW	Orange	50	13A	12	32
02209	16/2	SJTW	Orange	100	13A	6	31
Three Conductor							
02304	16/3	SJTW	Orange	10	13A	24	18
02211	16/3	SJTW	Black	10	13A	24	19
02305	16/3	SJTW	Orange	15	13A	18	24
02306	16/3	SJTW	Black	15	13A	18	24
02307	16/3	SJTW	Orange	25	13A	12	25
02308	16/3	SJTW	Orange	50	13A	12	46
02309	16/3	SJTW	Orange	100	10A	6	45
02407	14/3	SJTW	Red	25	15A	12	35
02408	14/3	SJTW	Red	50	15A	6	29
02409	14/3	SJTW	Red	100	13A	6	60
Three Conductor - Lighted End							
02587	12/3	SJTW	Yellow	25	15A	12	40
02588	12/3	SJTW	Yellow	50	15A	6	40
02589	12/3	SJTW	Yellow	100	15A	4	52
02687	10/3	SJTW	Yellow	25	15A*	6	36
02688	10/3	SJTW	Yellow	50	15A*	4	48
02689	10/3	SJTW	Yellow	100	15A*	3	70
Three Conductor Large Cap and Conductor - 600 Volt Rated							
02457	14/3	STW	Orange	25	15A	6	26
02458	14/3	STW	Orange	50	15A	4	34
02459	14/3	STW	Orange	100	15A	3	50
02557	12/3	STW	Orange	25	15A	6	34
02558	12/3	STW	Orange	50	15A	4	45
02559	12/3	STW	Orange	100	15A	3	65
<i>*Cap and Connector rated 15A</i>							

COLEMAN CABLE

Vinyl Outdoor Extension Cords
Landscape

These all-purpose cords resist moisture, abrasion, and prolonged exposure to sunlight for durability. Available in green, white, or beige to blend with grass, patios, and decks.




Mfg Part#	Wire	Wire	Color	Length	125V	Master Pk Qty	Master Pk Qty	Master Pk Wt
Three Conductor								
02352-05	16/3	SJTW	Green	20	13A	12	17	
02352-01	16/3	SJTW	White	20	13A	12	17	
02352-23	16/3	SJTW	Beige	20	13A	12	17	
02356-05	16/3	SJTW	Green	40	13A	12	37	
02356-11	16/3	SJTW	White	40	13A	12	37	
02356-23	16/3	SJTW	Beige	40	13A	12	37	
02353-05	16/3	SJTW	Green	80	10A	6	37	
02353-01	16/3	SJTW	White	80	10A	6	37	
02353-23	16/3	SJTW	Beige	80	10A	6	37	
Tri-Source® Three-Way Power Block								
02357-23	16/3	SJTW	Beige	40	13A	8	24	
02358-05	16/3	SJTW	Green	20	13A	8	11	

COLEMAN CABLE

Replacement Plugs and Connectors
NEMA 5-15 15A 125v Straight Blade

All jobsites require rugged, safe replacement wiring devices when the need arises. Safety issues lead to a heavier-duty design able to withstand harsh job-site conditions. Construction-Grade devices have tough, vinyl or nylon housing with many built-in features for speed, safety and assembly convenience. 15A, 20A, new 30A and 50A models address a wide range of customer needs, including locking 20A-50A applications. Industrial-Grade 15A devices have high visibility yellow housings designed for extended life for harsh, abusive IP20 and IP55 applications. Watertight-Grade 15A devices all have high visibility yellow housings designed for IP20 and IP55 applications where water is prevalent.



Mfg Part#	Desc.	Connection	Color	Duty	125V	Master Pk Qty	Master Pk Qty	Master Pk Wt
05984	NEMA 5-15 Vinyl	Male Plug	Yellow	Const	15A	20	1	
05985	NEMA 5-15 Vinyl	Female Plug	Yellow	Const	15A	20	1	
05966	NEMA 5-15	Male Plug	-	Const	15A	10	1.5	
05967	NEMA 5-15	Lighted Female	-	Const	15A	10	1.5	
05990	NEMA 5-15	1447 Male Plug	Yellow	Ind	15A	10	1.5	
05991	NEMA 5-15	1547 Female Plug	Yellow	Ind	15A	10	2	
05992	NEMA 5-15	14W47 Male Plug	Yellow	Water tight	15A	10	2	
05993	NEMA 5-15	15W47 Female	Yellow	Water tight	15A	10	3.5	

COLEMAN CABLE

Replacement Plugs and Connectors
NEMA L5-20 20A 125v Locking

All jobsites require rugged, safe replacement wiring devices when the need arises. Safety issues lead to a heavier-duty design able to withstand harsh job-site conditions. Construction-Grade devices have tough, vinyl or nylon housing with many built-in features for speed, safety and assembly convenience. 15A, 20A, new 30A and 50A models address a wide range of customer needs, including locking 20A-50A applications. Industrial-Grade 15A devices have high visibility yellow housings designed for extended life for harsh, abusive IP20 and IP55 applications. Watertight-Grade 15A devices all have high visibility yellow housings designed for IP20 and IP55 applications where water is prevalent.



Mfg Part#	Desc.	Connection	Duty	125V	Master Pk Qty	Master Pk Qty	Master Pk Wt
05986	NEMA L5-20P	Male Plug	Construction	20A	10	2.5	
05987	NEMA L5-20C	Female Connector	Construction	20A	10	3	

COLEMAN CABLE

Replacement Plugs and Connectors
NEMA L5-30 30A 125v Locking

All jobsites require rugged, safe replacement wiring devices when the need arises. Safety issues lead to a heavier-duty design able to withstand harsh job-site conditions. Construction-Grade devices have tough, vinyl or nylon housing with many built-in features for speed, safety and assembly convenience. 15A, 20A, new 30A and 50A models address a wide range of customer needs, including locking 20A-50A applications. Industrial-Grade 15A devices have high visibility yellow housings designed for extended life for harsh, abusive IP20 and IP55 applications. Watertight-Grade 15A devices all have high visibility yellow housings designed for IP20 and IP55 applications where water is prevalent.



Mfg Part#	Desc.	Connection	Duty	125V	Master Pk Qty	Master Pk Qty	Master Pk Wt
05962	NEMA L5-30	Male Plug	Construction	30A	10	2.5	
05963	NEMA L5-30	Female Connector	Construction	30A	10	3	

COLEMAN CABLE

Replacement Plugs and Connectors NEMA L6-30 30A 250v Locking

All jobsites require rugged, safe replacement wiring devices when the need arises. Safety issues lead to a heavier-duty design able to withstand harsh job-site conditions. Construction-Grade devices have tough, vinyl or nylon housing with many built-in features for speed, safety and assembly convenience. 15A, 20A, new 30A and 50A models address a wide range of customer needs, including locking 20A-50A applications. Industrial-Grade 15A devices have high visibility yellow housings designed for extended life for harsh, abusive IP20 and IP55 applications. Watertight-Grade 15A devices all have high visibility yellow housings designed for IP20 and IP55 applications where water is prevalent.



Mfg Part#	Desc.	Connection	Duty	125V	Master Pk Qty	Master Pk Wt
05964	NEMA L6-30	Male Plug	Construction	30A	10	2.5
05965	NEMA L6-30	Female Connector	Construction	30A	10	2.5

COLEMAN CABLE

Replacement Plugs and Connectors 50A 125/250v Locking

All jobsites require rugged, safe replacement wiring devices when the need arises. Safety issues lead to a heavier-duty design able to withstand harsh job-site conditions. Construction-Grade devices have tough, vinyl or nylon housing with many built-in features for speed, safety and assembly convenience. 15A, 20A, new 30A and 50A models address a wide range of customer needs, including locking 20A-50A applications. Industrial-Grade 15A devices have high visibility yellow housings designed for extended life for harsh, abusive IP20 and IP55 applications. Watertight-Grade 15A devices all have high visibility yellow housings designed for IP20 and IP55 applications where water is prevalent.



Mfg Part#	Desc.	Connection	Color	Duty	125V	Master Pk Qty	Master Pk Wt
05974	Locking Maringo	Male Plug	Black	Const	50A	4	5
05975	Locking Maringo	Female Connector	Black	Const	50A	4	4.2
05958	Locking	Male Plug	Black	Const	50A	4	5
05959	Locking	Female Connector	Black	Const	50A	4	4.2

COLEMAN CABLE

Generator Power Cords and Adapters



Mfg Part#	Description	Length	Master Pk Qty	Master Pk Wt
02618-88-02	10/3 SJTOW 5-20P to Lighted 5-20R	50	2	22
02619-88-02	10/3 SJTOW 5-20P to Lighted 5-20R	100	2	45
09058-88-02	10/3 SJTOW L5-20P to Lighted L5-20R	50	2	22
09059-88-02	10/3 SJTOW L5-20P to Lighted L5-20R	100	2	45

COLEMAN CABLE

Generator Power Cord Adapters Twist-To-Lock

UL listed - Meet OSHA specifications
Twist-to-lock extension cords and adapters designed for use in construction and industrial applications where extra protection and durability are needed. All are constructed with heavy-duty 12 gauge wire and molded locking male and female connectors.
Wire Type: STW
Color: Yellow



Mfg Part#	Plug	Receptacle	Wire Length	Master Pk Qty	Master Pk Wt
Adapters					
09020	Standard 15A U-Ground	Twist-to-Lock 20A	12/3 9 in.	10	5
09021	Twist-to-Lock 20A	Standard 15A U-Ground	12/3 9 in.	10	6
Y-Adapter					
09022	Twist-to-Lock 20A	Twist-to-Lock 20A	12/3 20 in.	10	14
W-Adapter					
09023	Twist-to-Lock 20A	Twist-to-Lock 20A	12/3 20 in.	10	16
Tri-Source®					
09084	Twist-to-Lock 20A	Standard 15A U-Ground	12/3 24 in.	10	15

COLEMAN CABLE

Generator Power Cords and Adapters



Mfg Part#	Description	Length	Master Pk Qty	Master Pk Wt
01914-88-02	10/3 STOW "Y" L5-30P to 2 Lighted L5-20R	3	4	11
01915-88-02	10/3 STOW "Y" L5-30P to 2 Lighted 5-20R	3	4	11
01923-88-02	12/4 STOW "Y" L14-20P to 12/3 2 Lighted L5-20R	3	4	12
01924-88-02	12/4 STOW "Y" L14-20P to 12/3 2 Lighted	3	4	12
01933-88-02	10/4 STOW "Y" L14-30P to 10/3 2 Lighted L5-20R	3	4	11
01934-88-02	10/4 STOW "Y" L14-30P to 10/3 2 Lighted 5-20R	3	4	11

COLEMAN CABLE

Generator Power Cords and Adapters



Mfg Part#	Description	Length	Master Pk Qty	Master Pk Wt
09084-88-02	12/3 STW L5-20P to Lighted Tri-Source	2	6	10

COLEMAN CABLE

Generator Power Cords and Adapters



Mfg Part#	Description	Length	Master Pk Qty	Master Pk Wt
02861-00-02	10/3 STOW "Y" L5-30P GFCI to (2) Lighted L5-20R	3	2	6
02862-00-02	10/3 STOW "Y" L5-30P GFCI to (2) Lighted 5-20R	3	2	6

COLEMAN CABLE

Generator Power Cords

Temporary power cord with three 15 amp receptacles and one male plug engineered to work exclusively with generators or other equipment rated to or less than 15 amps.



Mfg Part#	Wire GA/Cond.	Desc.	Wire Type	Length	Master Pk Qty	Master Pk Wt
01910	12/3	5-15P male	SJTW	25	12	44.5
01911	10/3	5-20P male	SJTW	25	6	36.5
01912	10/3	L5-30P male	SJTW	25	6	35.6

COLEMAN CABLE

Generator Power Cords

Twist-to-Lock



Mfg Part#	Wire	Wire	Length	125V	Master Pk Qty	Master Pk Wt
<i>SJTW Extension Cords (NEMA L5-20P to NEMA L5-20R)</i>						
09208	12/3	SJTW	50	20A	6	41
09209	12/3	SJTW	100	15A	4	52
<i>STW Extension Cords (NEMA L5-20P to NEMA L5-20R) -600 Volt</i>						
09028	12/3	STW	50	20A	4	40
09029	12/3	STW	100	15A	3	60

COLEMAN CABLE

Generator Power Cord Adapters

Vinyl "Y" and "W" Adapters

Mfg Part#	Wire	Wire Type	Length	Master Pk Qty	Master Pk Wt
<i>15A Y-Adapter</i>					
09018	12/3	STW	2	12	20
<i>15A W-Adapter</i>					
09019	12/3	STW	2	12	25

COLEMAN CABLE

Cord Storage

Coleman Cable's new storage devices are ideal for storage of Coleman Cable Cords.



Mfg Part#	Color	Max Cap (ft)	Master Pk Qty	Master Pk Wt
03527	Orange	100	12	6
03526	Orange	100	6	14
03524	Orange	200	6	12
04900	Red	200	15	1.88

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters

User Attachable

Convert your extension cords, tools, and equipment to add GFCI protection.



Mfg Part#	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02831	15A 120V/1800W UL/CSA Listed	15A	10	7

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters

In-Line

Tri-Source®

Provide personal protection from ground faults and open neutral conditions anywhere electrical equipment is used. All GFCIs are compact, weatherproof/rainproof and engineered to handle rugged conditions of any jobsite. All models feature molded connectors, 12 or 14 gauge OSHA safety yellow cords, heavy-duty strain relief, reinforced blades and pins, manual "Test/Reset" buttons, and industrial grade relays.

In-Line models offer a variety of receptacles with 20A and 30A relay units.



Mfg Part#	Length	Desc.	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02841	2.5	12/3 SJTW	15A 120V/1800W UL/CSA Listed	20A	6	6
02851	2.5	12/3 SEOW Heavy-Duty	15A 120V/1800W UL Listed	30A	6	8

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters
Right Angle

Tri-Source®

Provide personal protection from ground faults and open neutral conditions anywhere electrical equipment is used. All GFCIs are compact, weatherproof/rainproof and engineered to handle rugged conditions of any jobsite. All models feature molded connectors, 12 or 14 gauge OSHA safety yellow cords, heavy-duty strain relief, reinforced blades and pins, manual "Test/Reset" buttons, and industrial grade relays.



Right Angle models offer a variety of receptacles and cord lengths that are perfect where space is at a premium.

Mfg Part#	Length	Desc.	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02832	2	12/3 SJTW	15A 120V/180W	15A	6	9
02837	25	12/3 SJEOW	15A 120V/180W	15A	6	25
02838	50	12/3 SJEOW	15A 120V/180W	15A	6	43
02839	100	12/3 SJEOW	15A 120V/180W	15A	4	52
03392	2	12/3 SJTW	15A 120V/180W	15A	4	6
02834	2	12/3 SJTW	15A 120V/180W	15A	6	7

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters
Duplex Boxes

Provide personal protection from ground faults and open neutral conditions anywhere electrical equipment is used. All GFCIs are compact, weatherproof/rainproof and engineered to handle rugged conditions of any jobsite. All models feature molded connectors, 12 or 14 gauge OSHA safety yellow cords, heavy-duty strain relief, reinforced blades and pins, manual "Test/Reset" buttons, and industrial grade relays.



High impact resin with a slant-roof design prevent water entry. Receptacles can accommodate large plugs.

Mfg Part#	Length	Desc.	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02822	6	12/3 SJTW	15A 120V/1800W	25A	6	15
02827	25	14/3 SJEOW	15A 120V/1800W	25A	1	3
02828	50	14/3 SJEOW	15A 120V/1800W	25A	1	5

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters
Plug-In with Surge Protection

Converts any standard receptacle into a GFCI surge protected outlet.



Mfg Part#	Desc.	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02800	15A GFCI Converter for Std. Recep.	15A 120V/1800W UL Listed	15A	12	8

COLEMAN CABLE

GFCI - Ground Fault Circuit Interrupters
Quad Boxes

Provide personal protection from ground faults and open neutral conditions anywhere electrical equipment is used. All GFCIs are compact, weatherproof/rainproof and engineered to handle rugged conditions of any jobsite. All models feature molded connectors, 12 or 14 gauge OSHA safety yellow cords, heavy-duty strain relief, reinforced blades and pins, manual "Test/Reset" buttons, and industrial grade relays.



High impact resin with a slant-roof design prevent water entry. Receptacles can accommodate large plugs.

Mfg Part#	Length	Desc.	Amp/Volt/	Relay	Master Pk Qty	Master Pk Wt
02816	6	12/3 SJTW	15A 120V/1800W	25A	2	6
02821	6	12/3 SJTW	20A 120V/1800W	25A	2	6

COLEMAN CABLE

Power Distribution Center
Jobsite Electrical Hook Up
X-Treme Box™

The X-Treme Box™ is a portable, flexible, rugged and reliable power distribution center for all jobsite conditions. It is an economical solution for electrical hook up on any work-site. For expandability, run up to four boxes at 400ft. in series before significant voltage drop occurs. A heavy-gauge carbon-steel case with corrosion resistant finish and a steel-reinforced sled base offer excellent durability. The X-Treme Box™ offers the most advanced GFCI technology to virtually eliminate the possibility of electrical shock. Box features seven overload protected outlets, with GFCI, open neutral and over-voltage protection. Rainproof NEMA 3R enclosure.



Mfg Part#	Portable Power	50A Power	20A Power Outlets	Master Pk Qty	Master Pk Wt
01960	Rainproof NEMA 3R	125/250v	6-20A 125v 5-20R	1	34
01970	Rainproof NEMA 3R	125/250v	6-20A 125v 5-20R	1	34

COLEMAN CABLE

Power Distribution Extension Cords
for the X-Treme Box™

Rugged temporary power cords are designed for use with the X-Treme Box™ to handle 50A 3-Pole/4-Wire 125/250v AC.



Mfg Part#	Wire	End	Color	Length	Master Pk	Master Pk
01918	SEOW	Marino	Black	50	1	27
01919	SEOW	Marino	Black	100	1	54
01938	SEOW	Hubell	Black	50	1	27
01939	SEOW	Hubell	Black	100	1	54
02918	STW	Marino	Black	50	1	29
02919	STW	Marino	Black	100	1	57
02938	STW	Hubell	Black	50	1	29
02939	STW	Hubell	Black	100	1	57

COLEMAN CABLE

Power Distribution Center
Jobsite Electrical Hook Up
X-Treme Box™



The X-Treme Box™ is a portable, flexible, rugged and reliable power distribution center for all jobsite conditions. It is an economical solution for electrical hook up on any worksite. For expandability, run up to four boxes at 400ft. in series before significant voltage drop occurs. A heavy-gauge carbon-steel case with corrosion resistant finish and a steel-reinforced sled base offer excellent durability. The X-Treme Box™ offers the most advanced GFCI technology to virtually eliminate the possibility of electrical shock. Box features seven overload protected outlets, with GFCI, open neutral and over-voltage protection.

Mfg Part#	Portable Power	50A Power	20A Power Outlets	Master Pk Qty	Master Pk Wt
01950	NEMA Type 1	125/250v	6-20A 125v L5-20R	1	34

COLEMAN CABLE

Halogen Work Lights
Heat Lamps
Luma-Site®



An ideal temporary heat source for pig and chicken brooders. Insulated two-piece porcelain sockets with heavy-gauge aluminum reflectors, hang-up hooks and optional clamp.

Mfg Part#	Wire GA/Cond.	Wire Type	Length (ft.)	Master Pk Qty	Master Pk Wt
05968	18/2	SJT	8	6	12
05961	18/2	SJT	8	6	20

COLEMAN CABLE

Halogen Work Lights
Floodlight Series
Luma-Site®



This model features a pivoting head that allows the 500 watts of "Instant-On" light to move in any direction and an adjustable pivot handle (no tripod or telescoping base). It has a convenient on/off power switch, and is easily transported from site-to-site and stores easily. Coleman Cable's Luma-Site® Floodlight Series is reliable and powerful enough for basic needs.

Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07775	500 Watt Light, pivoting handle, yellow	6	36

COLEMAN CABLE

Cord Reels
Luma-Site®



Tired of tripping over extension cords? Luma-Site® Retractable Reels solve that problem and keep your work area organized. Reel cases are constructed with extra-tuff ABS plastic or heavy-duty steel and mount easily for use in workshop, basement, or garage. Mounting hardware included.

Mfg Part#	Wire	Wire Color	Length	125V	Master Pk Qty	Master Pk Wt
Cord Reel with U-Lock™ Outlet						
04632-88-08	16/3	SJT Black	30	10A	4	36
Cord Reel with Trinector®						
04633-88-08	16/3	SJT Black	30	10A	4	36
Heavy Duty Cord Reel w/ Lighted Tri-Source®						
04820-88-02	12/3	SJTW Yellow	50	15A	1	18
Trouble Light with Metal Guard and Plastic Reel w/Outlet						
05360-88-08	18/3	SVT Black	20	7A	4	15
Trouble Light with Metal Guard w/Outlet						
05380-88-08	18/3	SVT Black	50	6A	4	36
05570-88-08	16/3	SJT Black	30	10A	4	36
13 Watt Fluorescent with Outlet						
05937-88-04	16/3	SJT Black	30	na	4	30
26 Watt Fluorescent with Outlet						
05363-88-08	16/3	SJT Black	30	10A	4	28
13 Watt Plastic Reel Fluorescent						
05935-88-04	18/2	SJT Black	20	na	26	25
Trouble Light with Plastic Guard						
05302-88-08	18/2	SJT Black	2	75W	12	14
13 Watt Fluorescent with Outlet						
05998-88-08	16/3	SJT Black	2	13A	6	8

COLEMAN CABLE

Halogen Work Light
Replacement Parts



Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07818	Glass for part numbers 07775, 07776, and 07777	1	1
07819	Glass for part numbers 07765 and 07766	1	1
07880	500W Halogen Bulb	1	1

COLEMAN CABLE

Halogen Work Lights
Floodlight Series

Luma-Site®

These models feature sturdy tripod footing, pivoting heads that allow to direct the 500 watts of "Instant-On" light in any direction and a telescoping post that extends up to 7 feet. They feature a convenient on/off power switch, are easily transported from site-to-site and collapse for easy storage. Coleman Cable's Luma-Site® Floodlight Series is reliable and powerful enough for basic needs.



Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07776	Two Lights w/ separate on/off switches, yellow, tripod base	2	36
07777	Single Light, yellow, hand held base and tripod included.	3	-

COLEMAN CABLE

Halogen Work Lights
Premium Series

Luma-Site®

These models feature sturdy tripod footing, pivoting heads that allow to direct the 500 watts of "Instant-On" light in any direction and a telescoping post that extends up to 7 feet. They feature a convenient on/off power switch, are easily transported from site-to-site and collapse for easy storage. Coleman Cable's Luma-Site® Premium Series feature larger heads for better lighting and heavy gauge steel guards to resist damage.



Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07764	500W , sled base, tripod base, pivoting head, on/off swith, red.	2	38
07765	500W, hand-held, padded handle, sled base, on/off switch, red.	6	38
07766	500W 1000W pivoting head, tripod base, on/off switch, red, bulb storage compartment and 600W bulb included.	2	41

COLEMAN CABLE

Metal Halide Replacement Guards

Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07620	"0" Replacement bulb	4	4.41
07621	10" Wire reflector guard replacement	2	2.2
07622	16" Reflector replacement guard	2	4.41



COLEMAN CABLE

Metal Halide Temporary Lights
Temporary Lighting

All Cord-O-Lite lighting systems are 12/3 SJTW 300v.
All are UL, NEC, & OSHA Compliant.



Mfg Part#	Watts	Length	Guard	Master Pk Qty	Master Pk Wt
07601	400	6	16" Dome	2	54
07602	400	6	10" Wire	1	26
07603	400	6	10" Wire Dome	1	26

COLEMAN CABLE

Stringer Lights

Temporary Lighting

Cord-O-Lite®

Our most rugged lighting system. Heavy duty 12/3 SJTW (yellow) cord with molded light sockets. Accommodates A-23 type bulbs up to 150 watts. Available with easy-open plated-metal lamp guards, or snap-on plastic guards. Standard 15 amp molded or 20 amp locking ends. All Cord-O-Lite lighting systems are 12/3 SJTW 300v. All are UL, NEC, & OSHA Compliant.



Mfg Part#	Length	Guard	NEMA Plug	NEMA Receptacle	Master Pk Qty	Master Pk Wt
15 Amp						
07538	50	*Coated Metal	5-15P	5-15R	1	11
07539	100	*Coated Metal	5-15P	5-15R	1	27
07548	50	Plastic	5-15P	5-15R	1	9
07549	100	Plastic	5-15P	5-15R	1	25
07598**	50	*Coated Metal	5-15P	5-15R	1	16
07599**	100	*Coated Metal	5-15P	5-15R	1	30
20 Amp						
07558	50	Coated Metal	L5-20P	L5-20R	1	12
07559	100	Coated Metal	L5-20P	L5-20R	1	27
07568	50	Plastic	L5-20P	L5-20R	1	9
07569	100	Plastic	L5-20P	L5-20R	1	25
07588**	50	*Coated Metal	L5-20P	L5-20R	1	16
07589**	100	*Coated Metal	L5-20P	L5-20R	1	30

*Guards are pre-assembled onto lamp sockets

**CSA

COLEMAN CABLE

Stringer Light Replacement Guards

Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
07200-20	Coated Metal	20	6
07300	Plastic	20	2
07500-00-00	Plastic	20	3



COLEMAN CABLE

Stringer Lights
Temporary Lighting
Economy Cord-O-Lite®

Guards are pre-assembled onto lamp sockets to save labor and installation time. All Cord-O-Lite lighting systems are 12/3 SJTW 300v. All are UL, NEC, & OSHA Compliant.



Mfg Part#	Length	Guard	NEMA Plug	Master Pk Qty	Master Pk Wt
07145	100	Plastic	5-15P	1	14

COLEMAN CABLE

Stringer Lights
Temporary Lighting
Economy Cord-O-Lite®

This economical system features a 14/2 FY cable assembly (yellow) and our easy-open, snap-on plastic guards. Accommodates A-23 type bulbs up to 150 watts. Does not include caps or connectors. All Cord-O-Lite lighting systems are 12/3 SJTW 300v. All are UL, NEC, & OSHA Compliant.



Mfg Part#	Length	Guard	Master Pk Qty	Master Pk Wt
07128	50	Plastic	1	4
07129	100	Plastic	1	8

COLEMAN CABLE

Work Lights
Luma-Site®

Luma-Site® Work Lights represent both durability and practicality. Lightweight construction makes handling them effortless, but don't let the lack of weight fool you! Constructed from tough PVC, these lights can stand the rigors of almost any work environment. All Luma-Site® Work Lights come standard with power switches and bulb cages for fast light bulb changes. 75 Watt bulb maximum. Wire Type: SJT Color: Orange



Mfg Part#	Wire Length	125V	Master Pk Qty	Master Pk Wt
-----------	-------------	------	---------------	--------------

Two Conductor, Polypropylene Guard with Switch

05006	18/2	15	75W	12	14
05007	18/2	25	75W	12	19
05008	18/2	50	75W	12	19

Three Conductor, Polypropylene Guard with Outlet and Switch

05307	18/3	25	10A	12	22
05407	16/3	25	13A	6	13
05408	16/3	50	13A	6	24

Three Conductor, Grounded Metal Guard with Side Outlet and Switch

05327	18/3	25	10A	12	23
05328	16/3	50	10A	6	20
05427	16/3	25	13A	12	28
05428	16/3	50	13A	6	24

COLEMAN CABLE

Stringer Lights
Temporary Lighting
Econo-Lite® Streamer

This economical system features a 14 gauge (open conductors) and our easy-open, snap-on plastic guards. Accommodates A-23 type bulbs up to 150 watts. Does not include caps or connectors. All Cord-O-Lite lighting systems are 12/3 SJTW 300v. All are UL, NEC, & OSHA Compliant.



Mfg Part#	Length	Guard	Master Pk Qty	Master Pk Wt
07308	50	Plastic	1	3
07309	100	Plastic	1	5

COLEMAN CABLE

Work Lights - Heavy Duty
With Metal Guard
Polar/Solar®

Heavy-duty work lights featuring Coleman's exclusive T*Prene® insulated Polar/Solar® cord. Stays flexible under all temperature extremes to -67°F. Exclusive one-piece injection molded handle. Grounded, vinyl coated metal guard with switch and side outlet. 75 Watt maximum bulb. Oil and chemical resistant. Wire Type: SJEO Color: Yellow



Mfg Part#	Wire	Length	125V	Master Pk Qty	Master Pk Wt
05657	14/3	25	15A	6	6
05658	14/3	50	15A	6	30
05857	16/3	25	13A	6	13
05858	16/3	50	13A	6	23
<i>Industrial Work Lights</i>					
05337*	18/3	25	10A	12	26
05338*	18/3	50	10A	6	21

**Note: These products do not have a switch or outlet*

COLEMAN CABLE

Heavy Duty Reflector Lights
Luma-Site®

Versatile multi-use utility lamps with polished and vented aluminum reflector. Each unit features a double ball universal joint, non-marring grips, and a clamp-on bracket, on/off push-through switch and rugged molded-on plug.



Mfg Part#	Wire GA/ Cond.	Wire Type	Length (ft.)	Master Pk Qty	Master Pk Wt
05922	18/2	SPT	6	12	6
05932	18/2	SPT	6	12	11
05939	18/2	SPT	6	12	12
05946	18/2	SJT	15	12	17
05956	18/2	SJT	15	12	17

COLEMAN CABLE

Fluorescent Work Lights
Luma-Site®



Engineered to provide maximum light, Luma-Site® Fluorescent Lights were created specifically for the professional. A compact casing ensures the light can be placed in the tightest of spots and a convenient on/off switch guarantees you will have glare-free light only when you are ready. The ergonomic design means the light will sit comfortably in your hand even after a continued period of time. Should you need to work using both hands, a collapsible swivel hook allows you to hang the light in virtually any direction.

Wire Type: SJT (Fluorescent Tube Lights are SJTW)

Mfg Part#	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
26 Watt with Outlet & Detachable Magnet						
05364-88-08	16/3	Black	25	13A	4	16
26 Watt with Outlet						
05926-88-08	26 16/3	Black	10	13A	4	8
13 Watt with Outlet						
05929-88-04	16/3	Red	15	13A	6	13
26 Watt with Outlet, Wall Bracket and Detachable Magnet						
05999-88-08	16/3	Yellow	25	13A	6	21
13 Watt (no outlet)						
05930-88-02	18/2	Yellow	15	-	6	13
05931-88-02	18/2	Yellow	25	-	6	18
Fluorescent Tube Lights						
13 Watt Tube Light with On/Off Switch, Outlet and Two Hooks						
05927-88-08	18/2	Yellow	6	-	6	10
15 Watt Tube Light with On/Off Switch, Outlet and Two Hooks						
05928-88-08	16/3	Yellow	15	13A	4	15

COLEMAN CABLE

Luma-Site® Work Light
Replacement Parts

Mfg Part#	Desc.	Package	Master Pk Qty	Master Pk Wt
Replacement Work Light Guard				
05905	White Polypropylene	Bulk	12	3
05906	Metal Swing-open	Bulk	12	5
Replacement Work Light Guard Handle				
05906-97	Metal Swing-open Guard	Poly Bag	12	6
Work Light Repair Kit				
05912-97	Replacement handle and socket	Poly Bag	12	7
05896	Conductor handle with switch and side outlet	Poly Bag	6	7

COLEMAN CABLE

Rough Service Replacement Bulbs
Luma-Site®

Mfg Part#	Volt	Watt	Master Pk Qty	Master Pk Wt
05902	130	75	120	14
05903	130	100	120	14

COLEMAN CABLE

500 Watt Halogen Portable Worklight with Switch

DESIGNERS EDGE™

- "S" stand with foam grip handle and foam feet
- With easy light adjustment knob
- Weatherproof on/off switch
- 3' 18/3 grounded power cord
- UL & CUL listed



Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L33	500	Halogen	10,000	2000 hrs	6

COLEMAN CABLE

500 Watt Halogen Worklight Power Station

DESIGNERS EDGE™

- Cord storage reel converts most extension cords into four outlet power station
- For storage of extension cords. Holds up to 50 ft. of 12/3 gauge, 70 ft. of 14/3 or 90 ft. of 16/3 gauge cord
- Lightened on/off switch with circuit breaker
- Extra bulb storage tube
- Spare bulb included
- 14/3 grounded cord
- UL and CUL listed



Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L5509	500	Halogen	10,000	1500 hrs	2

COLEMAN CABLE

1000 Watt Double Bulb Halogen 160° Wide Angle Wall to Wall Portable Worklight

DESIGNERS EDGE™

- Patented design lights up to 160° per head
- Hinged style face frame
- Separate weatherproof on/off switches
- Extra bulb storage tube
- Wire storage brackets on leg
- Complete with three 500 watt halogen bulbs (one spare)
- 5' 18/3 Grounded Power Cord
- UL & CUL listed



Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L5203	1000	Halogen	16,000	2000 hrs	2

COLEMAN CABLE

Single Bulb 500 Watt Halogen Spring Mounted Power Light
DESIGNERS EDGE™



- Professional grade construction
- Light housing supported by stainless steel springs providing protection against impact, extending bulb life
- Heavy duty style roll cage gives maximum protection
- Extra bulb storage tube
- 10' 18/3 Grounded Power Cord
- UL & CUL listed

Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L113	500	Halogen	10,000	2000 hrs	2

COLEMAN CABLE

1400 Watt Double Bulb Halogen 2-N-1 Tripod Power Light
DESIGNERS EDGE™



- Heavy duty construction uses one 200 watt bulb and one 500 watt bulb in each housing for 700 watts per head, 1400 watts total
- Hinged style face frame
- Sled base and tripod base included
- Telescopes from 40" to 76" with "Easy Grip" locking nuts
- Adjustable extension leg for use on uneven surfaces
- Two extra bulb storage tubes
- Weatherproof on/off switches
- Complete with three 200 watt and three 500 watt halogen bulbs (one spare for each)
- UL & CUL listed

Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L5502	1400	Halogen	21,600	2000 hrs	2

COLEMAN CABLE

700 Watt Double Bulb Halogen Portable
DESIGNERS EDGE™



- Heavy duty construction uses one 200 and one 500 watt bulb for 700 watts total
- Hinged style face frame
- Large face frame and housing for cooler operation and longer bulb life
- Extra bulb storage tube
- Separate weatherproof on/off switches
- 5' 18/3 Grounded Power Cord
- Complete with two 200 watt and two 500 watt halogen bulbs (one spare for each)
- UL & CUL listed

Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L5500	700	Halogen	10,800	2000 hrs	4

COLEMAN CABLE

180 LED Eco-Zone Rechargeable Portable Worklight
DESIGNERS EDGE™



- Uses 180 Super Bright LEDs
- 50,000 hour rated LEDs give a super bright light that lasts up to 30 years
- Rechargeable Portable Design
- Weatherproof Switch
- Durable Polymeric housing
- High output mirror reflector
- Cool to the touch, great for indoor/outdoor use

Mfg Part#	Watts	Light Source	Lumens	Lamp Life	Master Pk
L1301	30+/-	LED	1200??	50,000? hrs	4

COLEMAN CABLE

108 LED Promotional Eco-Zone Portable Worklight
DESIGNERS EDGE™



- Uses 108 Super Bright LED's
- 50,000 hour rated LED. Lasts upto 30 years
- Cool to the touch. Great for indoor/outdoor use
- Weatherproof on/off switch
- 15 ft. cord with transformer
- Durable Polymeric housing
- High output mirrored reflector
- 1,200 lumen output

Mfg Part#	Light Source	Lumens	Lamp Life	Master Pk
L1306	LED	1200??	50,000? hrs	4

COLEMAN CABLE

65 Watt Fluorescent 360° Portable Worklight
DESIGNERS EDGE™



- Durable Polymeric housing
- Adjustable design allows the light to position at various angles allowing 360° lighting
- 6500K CFL 65W bulb included
- Weatherproof on/off switch
- Grounded outlet on base
- Great for indoor/outdoor use

Mfg Part#	Light Source	Lumens	Lamp Life	Master Pk
L2006	Fluorescent	4,300	8,000 hrs	4

COLEMAN CABLE

130 Watt (600 Watt Equivalent) 2-IN-1 Heavy Duty Fluorescent Worklight DESIGNERS EDGE™

- Two 65 watt fluorescent bulbs that last up to 5 times longer than halogen bulbs
- Sled and tripod base included
- Adjustable Extension Leg for use on uneven surfaces
- "Easy grip" quick locking nut
- Cool to the touch
- Extra heavy duty telescoping base - sled base and tripod base included
- 7' 18/3 Grounded Power Cord
- UL & CUL listed



Mfg Part#	Light Source	Lumens	Lamp Life	Master Pk
L2005	Fluorescent	8,600	10,000 hrs	1

COLEMAN CABLE

16 LED Cordless Trouble Light with Laser Pointer and 8 LED Spot Light DESIGNERS EDGE™

- 16 Super bright 10,000 hour rated LED's
- High Power LED spotlight for directional trouble shooting.
- Includes Laser Pointer
- On/off switch on handle operates light, laser and spotlight separately.
- Heavy duty magnet on handle
- Anti-roll design.
- Impact resistant aerospace grade aluminum body.
- AAA batteries included



Mfg Part#	Light Source	Colors Available	Lamp Life	Master Pk
L1407	LED	Silver, Blue, Red, and Black	10,000 hrs	12

COLEMAN CABLE

2000 Watt Industrial Double Head Metal Halide Power Light DESIGNERS EDGE™

- Mounted on a heavy duty telescoping pole and stand
- Telescopes from 6.25 to 10 feet tall
- Heavy duty tires with brake for easy mobility
- Includes Two 1,000 watt Metal Halide lamps
- 200,000 lumens of total light with both lights on
- 6,500 kelvin bright white light
- 12,000 hour average bulb life
- Die cast housing with hinged face for easy bulb changing
- Includes 2 weather proof switches and 15 ft. 12/3 grounded power cords with 30 amp grounded plugs
- 5 year limited warranty
- CSA listed, US and CA
- Stand can hold a portable generator (not included)



Mfg Part#	Light Source	Lumens	Lamp Life	Master Pk
L4211	Metal Halide	200,000	12,000 hrs	1

COLEMAN CABLE

2 & 4 Conductor Unshielded Type CM/CL2 Signal®

Power limited circuit and communication cable for non-riser applications. Used in control, signaling, systems, and Intercom /PA Systems. Approvals: UL Type CM/CL2 Outdoor, Article 725 & 800.

Mfg Part#	Gauge	Number of Conductors	Copper Stranding	Length	Pkg. Wt.
96238-05-09	22	4	Solid	500	7
51101-05-09	22	2	7x30	500	5
5112-05-09	22	4	7x30	500	7

COLEMAN CABLE

Area Network Cable Signal®

Power limited circuit and communication cable. Used in remote control, signaling, security systems, and Intercom/PA Systems, Sound/Audio, and Nurse Call. Approvals: UL Type CM/CL3R, NEC Article 725& 800, CUL Type CMG/FT4, California State Marshal.



Mfg Part#	Gauge	Number of Conductors	Copper Stranding	Length	Pkg. Wt.
Category 3					
96202-06-09	24	2	Solid	1000	10
96203-06-09	24	3	Solid	1000	13
96204-06-09	24	4	Solid	1000	17
96206-06-09	24	6	Solid	1000	24
Category 5e					
96263-46-09	24	4	Solid	1000	20
966956-46-06	24	4	Solid	1000	20
Category 6					
97272-16-09	23	4	Solid	1000	26

COLEMAN CABLE

Rechargeable 72 Super Bright LED Worklight DESIGNERS EDGE™

- Premium Lithium Rechargeable Battery
- 6 hour run time on full charge
- 120v Transformer and 12v Cigarette Charger Included
- On/Off Switch
- Fold down hanging hook
- Non-Slip Rubberize Grip
- Heavy duty 3mm Chrome Metal Grill
- Self Standing base
- 180 lumen output
- ETL listed for US and CA
- Colored charge indicator LED light shows when light is fully charged



Mfg Part#	Light Source	Lumens	Lamp Life	Master Pk
L1925	LED	180	10,000 hrs	4

COLEMAN CABLE

Coaxial Cable

Signal®

75 OHM Coaxial Cables for use in CCTV or CATV applications. Not for use in riser or plenum applications. RG59/U and RG6/U. Black PVC jacket.



Mfg Part#	Desc.	AWG	Dielectric Material	Length	Pkg.	Wt.
92001-05-08	RG6/U Type CATV CL2	18	Gas Injected	500	500	16
92003-05-08	RG6/U Type CATV CL2	18	Gas Injected	500	500	16
92006-05-08	RG59/U Type CATV CL2	22	Gas Injected	500	500	11
92074-05-08	RG59/U Type CATV CL2	20	Foamed	500	500	17
92041-05-08	RG6/U Type Quad-Shield CATV	18	Gas Injected	500	500	33

COLEMAN CABLE

Fire Alarm Cable

Signal®

Power limited fire alarm and communication cable for riser or non-riser applications. Used in Fire Systems, Smoke Detectors and Signaling Fire Protective Circuits. Approvals: UL Type FPLR, NEC Article 760, CUL Type CMG/FT4, California State Fire Marshal

Mfg Part#	AWG	Number of Conductors	Copper Stranding	Jacket Color	Length	Pkg.	Wt.
<i>Fire Alarm Multi-Conductor Cable-Unshielded Type</i>							
98820-05-04	18	2	Solid	Red	500	500	16
98804-05-04	18	4	Solid	Red	500	500	27
98620-05-04	16	2	Solid	Red	500	500	22
98604-05-04	16	4	Solid	Red	500	500	40
<i>Fire Alarm Parallel Zip Cable Type FPLR</i>							
97818-05-04	18	2	Solid	Red	500	500	9
97816-05-04	16	2	Solid	Red	500	500	12
97814-05-04	14	2	Solid	Red	500	500	19
<i>Fire Alarm Multi-Conductor Cable-Overall Shielded Type FPLR</i>							
98300-05-04	18	2	Solid	Red	500	500	10
98630-05-04	16	2	Solid	Red	500	500	13
<i>Fire Alarm Multi-Conductor Cable-Unshielded Plenum Type FPLR</i>							
85802-05-04	18		Solid	Red	500	500	10
85804-05-04	18		Solid	Red	500	500	17
85602-05-04	16		Solid	Red	500	500	24
85402-05-04	14		Solid	Red	500	500	24

COLEMAN CABLE

Multi-Conductor Cable

Overall Shielded Type CMR/CL3R

Signal®

Power limited circuit and communication cable. Used in remote control, signaling, security systems, and Intercom/PA Systems, Sound/Audio, and Nurse Call. Approvals: UL Type CM/CL3R, NEC Article 725& 800, CUL Type CMG/FT4, California State Marshal.



Mfg Part#	Gauge	Number of Conductors	Copper Stranding	Length	Pkg.	Wt.
95211-05-09	22	2	7x30	500	500	6
67001-05-09	22	4	7x30	500	500	9
95211-05-09	18	2	7x0.0152	500	500	11
67003-05-09	18	4	7x0.0152	500	500	19

COLEMAN CABLE

Multi-Conductor Cable

Unshielded Type CMR/CL3R

Signal®

Power limited circuit and communication cable. Used in remote control, signaling, security systems, and Intercom/PA Systems, Sound/Audio, and Nurse Call. Approvals: UL Type CM/CL3R, NEC Article 725& 800, CUL Type CMG/FT4, California State Marshal.



Mfg Part#	Gauge	Number of Conductors	Copper Stranding	Length	Pkg.	Wt.
51104-06-09	18	2	7x0.0152	1000	1000	7
51114-06-09	18	4	7x0.0152	1000	1000	28
51105-06-09	16	2	19x0.0117	1000	1000	24

COLEMAN CABLE

Bulk Vinyl Portable Cord

A firm compact cylindrical cord cabled for maximum flexibility and roundness per UL 62. Easy to remove jacket. Rated -20°C to 60°C. PVC cords provide excellent abrasion, ozone and chemical resistance.



Mfg Part#	Size	Type	Color	Length	Pkg.	Wt.
20205-66-03	18/2	SJTW	Orange	250	250	11
20305-66-03	18/3	SJTW	Orange	250	250	13
20206-66-03	16/2	SJTW	Orange	250	250	13
20306-66-03	16/3	SJTW	Orange	250	250	16
20307-66-03	14/3	SJTW	Orange	250	250	21
20308-66-03	12/3	SJTW	Orange	250	250	31
20309-04-03	10/3	SJTW	Orange	250	250	56

COLEMAN CABLE

Black Portable Cord

Seoprene® 105°C



Flexible and tough jacket. Offers a wide useable temperature range of -50°C to 105°C. Seoprene provides excellent abrasion, ozone, sunlight, chemical, oil, water, and mold resistance along with non-wicking lightweight polypropylene fillers. Water resistant with high dielectric insulation. Lightweight, long lasting, easy to carry and handle. All components are recyclable and non-hazardous for environmental landfill disposal. Federal and Military use under Federal Spec. JC-580B. UL Listed SE00W 600V and SJEOOW 300V to NEC

Mfg Part#	Size	Type	Color	Pkg. Wt	Length
23285-04-08	18/2	SJEW	Black	11	250
23385-04-08	18/3	SJEW	Black	14	250
23286-04-08	16/2	SJEW	Black	14	250
23386-04-08	16/3	SJEW	Black	17	250
23486-04-08	16/4	SJEW	Black	20	250
23287-04-08	14/2	SJEW	Black	17	250
23387-04-08	14/3	SJEW	Black	21	250
23487-04-08	14/4	SJEW	Black	26	250
23288-04-08	12/2	SJEW	Black	24	250
23388-04-08	12/3	SJEW	Black	31	250
23488-04-08	12/4	SJEW	Black	39	250
23389-66-08	10/3	SJEW	Black	22	100
23225-04-08	18/2	SJEOOW	Black	11	250
23325-04-08	18/3	SJEOOW	Black	14	250
23425-04-08	18/4	SJEOOW	Black	17	250
23226-04-08	16/2	SJEOOW	Black	14	250
23326-04-08	16/3	SJEOOW	Black	17	250
23426-04-08	16/4	SJEOOW	Black	20	250
23227-04-08	14/2	SJEOOW	Black	17	250
23327-04-08	14/3	SJEOOW	Black	21	250
23427-04-08	14/4	SJEOOW	Black	26	250
23228-04-08	12/2	SJEOOW	Black	25	250
23328-04-08	12/3	SJEOOW	Black	31	250
23428-04-08	12/4	SJEOOW	Black	40	250
23229-04-08	10/2	SJEOOW	Black	42	250
23329-04-08	10/3	SJEOOW	Black	54	250
23429-05-08	10/4	SJEOOW	Black	69	500
22225-04-08	18/2	SE00W	Black	15	250
22325-04-08	18/3	SE00W	Black	18	250
22226-04-08	16/2	SE00W	Black	18	250
22326-04-08	16/3	SE00W	Black	21	250
22227-05-08	14/2	SE00W	Black	63	500
22327-05-08	14/3	SE00W	Black	75	500
22427-05-08	14/4	SE00W	Black	92	500
22228-05-08	12/2	SE00W	Black	82	500
22328-05-08	12/3	SE00W	Black	100	500
22428-05-08	12/4	SE00W	Black	121	500
22229-05-08	10/2	SE00W	Black	104	500
22329-05-08	10/3	SE00W	Black	130	500
22429-05-08	10/4	SE00W	Black	158	500
22320-04-08	8/3	SE00W	Black	83	250
22420-04-08	8/4	SE00W	Black	107	250
22321-04-08	6/3	SE00W	Black	119	250
22421-04-08	6/4	SE00W	Black	149	250

COLEMAN CABLE

EPR Welding Cable

-40°C - 105°C



Excellent ozone, sun, weather, and chemical resistance. Foot-marked for easy length identification.

Mfg Part#	Wire	Stranding	Conductor	Jacket	Length	Pkg. Wt
10412	4	412/30	.366"	Black	250	43
10413	2	647/30	.429"	Black	250	64
10414	1	817/30	.508"	Black	250	86
10415	1/0	1027/30	.555"	Black	250	103
10416	2/0	1089/30	.598"	Black	250	126
10417	3/0	1650/30	.673"	Black	250	157
10418	4/0	2065/30	.716"	Black	250	195

COLEMAN CABLE

Welding Cable

Cut-to-Length



Mfg Part#	Wire	Stranding	Conductor	Jacket	Length	Pkg. Wt
10416C708	2/0			Black	25	25
10416C808	2/0			Black	50	25
10416C908	2/0			Black	100	25
<i>With Tweco Connectors</i>						
10416T808	2/0			Black	50	25
10416T908	2/0			Black	100	25

COLEMAN CABLE

Colflex Welding Cable

Supreme flexibility at extreme temperatures between -50°C and 105°C. Highly resistant to flame, oil, grease, solvents, ozone and abrasion. 600 volt, high dielectric strength integrity. Lightweight, heavy-duty jacket. Easy handling and storing.

Mfg Part#	Wire	Stranding	Conductor	Jacket	Length	Pkg. Wt
10010-04-08	8	7x 24/30	0.309"	Black	250	23
10011-04-08	6	7x 27/30	0.350"	Black	250	33
10012-04-08	4	7x 60/30	0.400"	Black	250	48
10013-04-08	2	19x 35/30	0.475"	Black	250	70
10014-04-08	1	19x 44/30	0.505"	Black	250	88
10015-04-08	1/0	19x 55/30	0.584"	Black	250	111
10016-04-08	2/0	19x 70/30	0.630"	Black	250	140
10017-04-08	3/0	19x 88/30	0.720"	Black	250	179
10018-04-08	4/0	19x 111/30	0.790"	Black	250	220
10779-04-08	250MCM	7x 7x 51/30	0.920"	Black	250	255
10784-04-08	350MCM	19x 7x 26/30	1.055"	Black	250	342
10789-04-08	500MCM	19x 7x 38/30	1.262"	Black	250	469



COLEMAN CABLE

Super Colflex Welding Cable

UL tested for crushing, impact, flame, sunlight, abrasion, and insulation resistance.

Mfg Part#	Wire	Stranding	Conductor	Jacket	Length	Pkg. Wt
10910	8	7x24/30	0.347"	Black	250	25
10911	6	7x37/30	0.388"	Black	250	35
10912	4	7x60/30	0.459"	Black	250	50
10913	2	19x35/30	0.532"	Black	250	75
10914	1	19x44/30	0.564"	Black	250	88
10915	1/0	19x55/30	0.604"	Black	250	113
10916	2/0	19x70/30	0.664"	Black	250	140
10917	3/0	19x88/30	0.702"	Black	250	170
10918	4/0	19x111/30	0.780"	Black	250	212
10919	250 MCM	7x7/51/30	0.922"	Black	250	308

COLEMAN CABLE

Heater Cord/TV Lead Wire/Vacuum Cord

Mfg Part#	Desc.	Wire Gauge	Jacket	Length	Pkg. Wt
60146-66-08	16/2 Heater Cord	16	Black	250	12
60148-04-07	Flat 300 Ohm TV Lead Wire	-	Brown	250	8
20105-66-09	18/2 Vacuum	18	Grey	250	11
20106-66-09	18/3 Vacuum	18	Grey	250	13

COLEMAN CABLE

Lamp Cord

For use with lamps and other small appliances

Mfg Part#	Wire Desc.	Jacket	Length	Pkg. Wt
60000-66-01	18/2 SPT-1 White	White	250	7
60000-66-07	18/2 SPT-1 Brown	Brown	250	7
60000-66-08	18/2 SPT-1 Black	Black	250	7
60000-66-18	18/2 SPT-1 Clear	Clear	250	7
60000-66-19	18/2 SPT-1 Gold	Gold	250	7
60000-66-21	18/2 SPT-1 Silver	Silver	250	7
60126-66-01	16/2 SPT-2 White	White	250	10
60126-66-07	16/2 SPT-2 Brown	Brown	250	10
60126-66-08	16/2 SPT-2 Black	Black	250	10

COLEMAN CABLE

MTW

Features extra flexible 30 AWG stranding. Rated as ASTM Class Flexing Service by NFPA 79 electrical standard for industrial machinery. Insulation, oil, moisture, and acid resistant. Approvals: NFPA 79 Electrical Standard for Industrial Machinery, NFPA 70 National Electric Code, UL1063 Machine Tool Wires and Cables, UL Subject 758 Appliance Wire and Material, CSA C22.2 No. 127 Equipment Wires, CSA C22.2 No. 210.1 Appliance Wiring Material Products, ASTM B174 Bunch Stranded Copper Conductors.

Mfg Part#	Wire	Stranding	Jacket	Length	Pkg. Wt
41101-05-01	18	16/30	White	500	3
41101-05-04	18	16/30	Red	500	3
41101-05-05	18	16/30	Green	500	3
41101-05-08	18	16/30	Black	500	3
41102-05-01	16	26/30	White	500	4
41102-05-04	16	26/30	Red	500	4
41102-05-05	16	26/30	Green	500	4
41102-05-08	16	26/30	Black	500	4

COLEMAN CABLE

TFFN

18 & 16 AWG Stranded Bare Copper. PVC/Nylon Insulation.

Mfg Part#	Conductor Size	Stranding	Jacket	Length	Pkg. Wt
51011-05-01	18	16/30	White	500	4
51011-05-04	18	16/30	Red	500	4
51011-05-05	18	16/30	Green	500	4
51011-05-08	18	16/30	Black	500	4
51012-05-01	16	26/30	White	500	6
51012-05-04	16	26/30	Red	500	6
51012-05-05	16	26/30	Green	500	6
51012-05-08	16	26/30	Black	500	6

COLEMAN CABLE

TFN

18 & 16 AWG Stranded Bare Copper. PVC/Nylon Insulation.

Mfg Part#	Conductor Size	Stranding	Jacket	Length	Pkg. Wt
51791-05-01	18	Solid	White	500	4
51791-05-04	18	Solid	Red	500	4
51791-05-05	18	Solid	Green	500	4
51791-05-08	18	Solid	Black	500	4
51792-05-01	16	Solid	White	500	6
51792-05-04	16	Solid	Red	500	6
51792-05-05	16	Solid	Green	500	6
51792-05-08	16	Solid	Black	500	6



COLEMAN CABLE

THHN

14 & 12 AWG Solid Bare Copper. PVC/Nylon Insulation.

Mfg Part#	Conductor Size	Stranding	Jacket	Length	Pkg. Wt
51041-05-01	14	Solid	White	500	9
51041-05-04	14	Solid	Red	500	9
51041-05-05	14	Solid	Green	500	9
51041-05-08	14	Solid	Black	500	9
51042-05-01	12	Solid	White	500	13
51042-05-04	12	Solid	Red	500	13
51042-05-05	12	Solid	Green	500	13
51042-05-08	12	Solid	Black	500	13

COLEMAN CABLE

Ground Rods

Copper plated steel rods used for grounding electrical current.

Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
93101-35-00	8 ft. x 1/2"	10	55
93104-35-00	8 ft. x 5/8"	10	71

COLEMAN CABLE

Multi-Conductor Sprinkler Cable

Baron™

Underground Sprinkler Cable - UL Listed - Direct Burial SOL BC30 Volt - PE Jacket with Ripcord

Mfg Part#	AWG # of Conductors	Jacket	Length	Pkg. Wt
54702-04-08	18	2	Black	250 20
54703-04-08	18	3	Black	250 26
54704-04-08	18	4	Black	250 33
54705-04-08	18	5	Black	250 40
54706-04-08	18	6	Black	250 46
54707-04-08	18	7	Black	250 61
54708-04-08	18	8	Black	250 67
54709-04-08	18	9	Black	250 74
54710-04-08	18	10	Black	250 81
54712-04-08	18	12	Black	250 91
54713-04-08	18	13	Black	250 97

COLEMAN CABLE

Bell Wire

Mfg Part#	AWG # of Conductors	Length	Master Pk Qty	Master Pk Wt
70102-66-32	20	2	500	1 5
70103-66-31	20	3	500	1 7

COLEMAN CABLE

Pump and Irrigation Cable

Baron™

Coleman Cable's Pump and Irrigation Cables supply all those little extras you have wished for, like finer stranding, more flexible insulation, improved abrasion resistance and permanent colors that won't fade over time.

Mfg Part#	Desc.	Stranding	Length	Pkg. Wt
<i>Superior Flat Parallel Pump Cable with Gound</i>				
42338	12/3 with 12GA Ground	65/30	1000 and 500	135
42339	10/3 with 10GA Ground	104/30	1000 and 500	192
<i>Standard Twisted Pump Cable (PVC) with Ground</i>				
42258	12/3 with 12GA Ground	Solid	1000 and 500	128
42359	10/3 with 10GA Ground	Solid	1000 and 500	186
<i>Standard Flat Jacketed Pump Cable (PVC/PVC) with Ground</i>				
42368	12/3 with 12GA Ground	19/0.0185	1000 and 500	201
42369	10/3 with 10GA Ground	19/0.0234	1000 and 500	268

COLEMAN CABLE

Multi-Conductor Underground Feeder

Baron™

Underground feeder cable for direct burial applications. Black and white conductors with bare ground. UL Standard 493.

Mfg Part#	AWG # of Conductors	Jacket	Length	Pkg. Wt
55560-06-09	14	2+ Gound	Grey	1000 83
55562-06-09	12	2+ Gound	Grey	1000 129
55564-06-09	10	2+ Gound	Grey	1000 174

COLEMAN CABLE

Single-Conductor Underground Feeder

Underground feeder cable for direct burial applications. UL Type UF, CULType TWU FT1

Mfg Part#	Gauge	Copper	Stranding	Jacket	Length	Master Pk Qty	Master Pk Wt
54501-05-01	14	Solid	White	500	4	56	
54501-05-04	14	Solid	Red	500	4	56	
54501-05-05	14	Solid	Green	500	4	56	
54501-05-08	14	Solid	Black	500	4	56	

COLEMAN CABLE

Thermostat Wire

Baron's popular thermostat wire is both UL, CUL, and ETL approved and is suitable for NEC article 725 applications. It is constructed with a PVC jacket and conductors insulated with polypropylene.

Mfg Part#	AWG	# of Conductors	Jacket Length	Master Pk Qty	Master Pk Wt
55202-05-07	20	2	Brown 500	4	20
55203-05-07	20	3	Brown 500	4	26
55204-04-07	20	4	Brown 250	4	17
55205-04-07	20	5	Brown 250	4	21
55206-04-07	20	6	Brown 250	4	25
55207-04-07	20	7	Brown 250	4	28
55208-04-07	20	8	Brown 250	4	31
55209-04-07	20	9	Brown 250	4	35
55210-04-07	20	10	Brown 250	4	38
55212-04-07	20	12	Brown 250	4	45
55302-05-07	18	2	Brown 500	4	28
55303-05-07	18	3	Brown 500	4	40
55304-04-07	18	4	Brown 250	4	26
55305-04-07	18	5	Brown 250	4	32
55306-04-07	18	6	Brown 250	4	38
55307-04-07	18	7	Brown 250	4	43
55308-04-07	18	8	Brown 250	4	48
55309-04-07	18	9	Brown 250	4	54
55310-04-07	18	10	Brown 250	4	60
55312-04-07	18	12	Brown 250	1	19

COLEMAN CABLE

Power Outlet Adapter 3-Way Solid Molded PVC



Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
3 to 1 Adaptor				
09901-00	Gray	Bulk	100	8
3 Outlet Adaptor-Plastic Housing				
09913	Beige	Blister	18	5
3-Way Adapter-Solid Molded PVC				
09902	Beige	Blister	18	7
09905	Green	Blister	18	7
09906-97-03	Orange	Blister	18	7
09906-88-03	Orange	Bulk	24	9

COLEMAN CABLE

Holiday Products

Mfg Part#	Wire GA	Wire Color	Length	125V	Master Pk Qty	Master Pk Wt
Holiday Cube Taps						
09453	16/2	SPT-2 Green	12	13A	36	14
09455	16/2	SPT-2 Green	20	13A	25	17
Christmas Tree Cube Tap with on/off foot switch						
09493	16/2	SPT-2 Green	9	7A	24	15
Christmas Tree Cube Tap with on/off dual switch						
09492	16/2	SPT-2 Green	9	7A	24	15
Outdoor Power Stake with Circuit Breaker and Outlet Covers						
05776	16/3	SJTW Green	15	13A	6	16
05777	16/3	SJTW Green	25	13A	6	15
Outdoor Digital Timer with Photo Electric Switch and Power Indicator						
04600	-	- Black	-	8A	12	16
Outdoor Remote Control with Transmitter and Receiver						
04602	-	- Black	-	8A	12	16
Floodlight Holder						
05706	18/2	SJTW Green	6	10A	18	14



COLEMAN CABLE

Indoor Extension Cords Cube Tap Extension Cords SlenderPlug™

Plug design allows you to move furniture closer to the wall and helps prevent cord and plug damage. SlenderPlug™ cube features an electro-luminescent lighted plug.

Mfg Part#	Wire GA/ Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
09407	16/2	SPT-2	Brown	7	24	9
09409	16/2	SPT-2	Brown	11	24	15
09417	16/2	SPT-2	White	7	24	9
09419	16/2	SPT-2	White	11	24	15



COLEMAN CABLE

Indoor Extension Cords Grounded 3 Outlet Trinector™ SlenderPlug™

Plug design allows you to move furniture closer to the wall and helps prevent cord and plug damage. The Trinector® receptacle has 3 grounded outlets.

Mfg Part#	Wire GA/ Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
03507	16/3	SPT-2	Beige	6	24	13
03508	16/3	SPT-2	Beige	12	24	18
03517	16/3	SPT-2	White	6	24	13
03518	16/3	SPT-2	White	12	24	18
03519	14/3	SJT	White	6	18	17



COLEMAN CABLE

Indoor Extension Cords
Cube Taps

Plug and three-outlet polarized connector for convenient use. Each connector has a safety cover or slide covers permanently attached.

Mfg Part#	Wire GA/Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
Cube Taps						
09401	16/2	SPT-2	Brown	6	48	15
09402	16/2	SPT-2	Brown	9	36	16
09403	16/2	SPT-2	Brown	12	36	20
09404	16/2	SPT-2	Brown	15	24	16
09405	16/2	SPT-2	Brown	20	24	19
09411	16/2	SPT-2	White	6	48	15
09412	16/2	SPT-2	White	9	36	16
09413	16/2	SPT-2	White	12	36	20
09414	16/2	SPT-2	White	15	24	16
09415	16/2	SPT-2	White	20	24	19
03520-01	16/3	SPT-2	White	8	24	15
03520-07	16/3	SPT-2	Brown	8	24	15
Remote Control Cord						
09345	16/2	SPT-2	White	15	24	26

COLEMAN CABLE

Indoor Extension Cords
Split Cube Taps

Cord splits in 2 directions-6 feet each direction



Mfg Part#	Wire GA/Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
09406	16/2	SPT-2	Green	12	24	15
09408	16/2	SPT-2	Brown	12	24	15
09418	16/2	SPT-2	White	12	24	15

COLEMAN CABLE

Appliance Cords
Air Conditioner/Major Appliance

Three conductor heavy duty flat vinyl. Right angle male plug. Strudy cord for use with air conditioners, power tools and major appliances. Grounded, right angle, male plugs guard against accidental disconnection.



Mfg Part#	Wire GA/Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
03531	14/3	SPT-3	Beige	3	36	22
03532	14/3	SPT-3	Beige	6	24	20
03533	14/3	SPT-3	Beige	9	18	18
03535	14/3	SPT-3	Beige	12	12	16
03536	14/3	SPT-3	Beige	15	12	19
03537	14/3	SPT-3	Beige	9	18	20

COLEMAN CABLE

Replacement Power Supply Cord
Three Conductor



Mfg Part#	Wire GA	Wire	Color	Length	125V	Master Pk Qty	Master Pk Wt
Two Conductor							
09853	16/2	SJEO	Black	6	13A	50	18
09854	16/2	SJEO	Black	9	13A	50	25
Three Conductor							
09855		SJEO	Black	6	13A	50	23
09856		SJEO	Black	9	13A	50	32
09857		SJEO	Black	6	15A	25	15
09858		SJEO	Black	9	15A	25	21
09702		SJTW	Black	6	13A	25	9
09703		SJTW	Black	3	13A	25	10
09706		SJTW	Black	6	13A	25	13
09709	16/3	SJTW	Black	9	13A	25	22
09716		SJTW	Black	6	15A	25	18
09719		SJTW	Black	9	15A	25	23
09733		SJTW	Gray	3	13A	25	6
09734		SPT-3	Gray	4	13A	25	9
09736		SPT-3	Gray	6	13A	25	12
09724		SPT-3	Gray	4	13A	25	9
09726		SPT-3	Gray	6	13A	25	12
09743		SPT-3	Gray	3	15A	25	10
09746		SPT-3	Gray	6	15A	25	18

COLEMAN CABLE

Appliance Cords
Range & Dryer Cords

Thick vinyl insulation with right angle male plug. Strain relief clamp helps prevent cord damage. Hardware included.



Mfg Part#	Wire GA/Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
Range Cords-Three Conductor, Flat Cord						
09014	6/2 & 8/1	SRDT	Gray	4	12	20
09015	6/2 & 8/1	SRDT	Gray	5	12	25
09016	6/2 & 8/1	SRDT	Gray	6	12	30
Range Cords-Four Conductor, Round Cord						
09044	6/2 & 8/2	SRDT	Black	4	12	34
09045	6/2 & 8/2	SRDT	Black	5	12	42
09046	6/2 & 8/2	SRDT	Black	6	12	50
Dryer Cords-Three Conductor, Flat Cord						
09124	10/3	SRDT	Gray	4	12	16
09125	10/3	SRDT	Gray	5	12	17
09126	10/3	SRDT	Gray	6	12	22
Dryer Cords-Four Conductor, Round Cord						
09154	10/4	SRDT	Black	4	12	26
09155	10/4	SRDT	Black	5	12	22
09156	10/4	SRDT	Black	6	12	24

COLEMAN CABLE

Small Appliance Cords



Mfg Part#	Wire GA/ Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
Coffee Maker, Frypan and Small Appliance Cords						
09303	18/2	HPN	Black	3	12	3
09306	18/2	HPN	Black	6	12	4
Office Machine Cord						
09307	18/2	SPT-2	White	6	12	4
Roaster, Broiler Appliance Cord						
09326	16/2	HPN	Black	6	12	4
Replacement Iron Cord						
09327	16/2	HPN	Black	6	12	4
Small Appliance Cord						
09316	18/2	HPN	Black	6	12	4
Small Appliance/Heater Extension Cord						
09336	16/2	HPN	Black	6	12	4

COLEMAN CABLE

Appliance Cords

Vacuum Cleaner

For indoor use only.

Mfg Part#	Wire GA/ Cond.	Wire Type	Color	Length	Master Pk Qty	Master Pk Wt
03528	16/2	SVT	Black	18	12	12

COLEMAN CABLE

Surge Protectors and Power Strips

8 Outlet Surge Protectors

PowerStation®



These 6 outlet surge protectors feature a unique housing with sliding outlet covers, automatic shutdown protection and an exclusive cord management system.

Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
8 Outlet Home Office Surge Protector with 2 line Phone Protection				
04652	Blk/Silver	Box	3	7
8 Outlet Home Theater Surge Protector with 2 line Coaxial and Splitter Phone line Protection				
04649	Blk/Silver	Box	3	7
8 Outlet Network Surge Protector with RJ-45 Data, Coaxial and Splitter Phone line Protection				
04653	Blk/Silver	Box	3	7

COLEMAN CABLE

Surge Protectors

Workshop



These Workshop strips, power centers and surge protectors are built to take abuse. Most products feature a built-in cord wrap and hang hole that make it easy to store when not in use.

Mfg Part#	Length (ft)	Color	Package	Master Pk Qty	Master Pk Wt
6 Outlet Strip					
04666	8	Blk/Yellow	Sleeve	6	8.5
4 Outlet GFCI Block					
04644	6	Blk/Yellow	Box	4	12.1
6 Outlet Metal Strip					
04654	6	Blk/Yellow	Box	6	12
6 Outlet Metal Strip					
04657	15	Blk/Yellow	Box	6	28
8 Outlet Metal Power Center					
04655	6	Blk/Yellow	Box	6	15
8 Outlet Metal Surge Center, 750 Joules					
04656	6	Blk/Yellow	Box	12	33

COLEMAN CABLE

Surge Protectors

6 Outlet



Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
6 Outlet Surge Protector				
04617	Ivory	Sleeve	24	20.5
6 Outlet Surge Protector with Safety Outlet Covers				
04623	White	Sleeve	24	25
6 Outlet Surge Protector				
04610	White	Sleeve	12	10.4
6 Outlet Metal Surge Protector				
04625	Ivory	Box	6	9.5
6 Outlet Metal Surge Protector with 12' Cord				
04628	Ivory	Box	12	34.2

COLEMAN CABLE

Surge Adapters

Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
1 Outlet Surge Adapter				
04635	Ivory	Blister Card		6.6
3 Outlet Surge Adapter				
04611	Ivory	Blister Card		8.6
6 Outlet Surge Adapter				
04612	White	Blister Card		16
6 Outlet Surge Adapter with Phone Line Protection				
04630	Ivory	Blister Card		14



COLEMAN CABLE

Surge Protectors and Power Strips
7 Outlet Surge Protectors
PowerStation®



These 7 outlet surge protectors feature a unique housing with 2 adaptor-spaced outlets, sliding outlet covers, automatic shutdown protection and an exclusive cord management system.

Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
7 Outlet Home Electronics Surge Protector				
04662	Blk/Gry	Box	6	12.12
7 Outlet TV/DVD Surge Protector with Coaxial Line Protection				
04663	Blk/Gry	Box	6	12.12
7 Outlet Personal Computer Surge Protector with Phone Line Protection				
04664	Blk/Gry	Box	6	12.12
7 Outlet Home Network Surge Protector with RJ-45 High Speed Data Line Protection				
04665	Blk/Gry	Box	6	12.12

COLEMAN CABLE

Power Strips



Mfg Part#	Length (ft)	Color	Package	Master Pk Qty	Master Pk Wt
6 Outlet Power Strip					
04616	4	Ivory	Sleeve	12	10.2
6 Outlet Strip with Safety Outlet Covers					
04622	4	White	Sleeve	24	11
6 Outlet Strip Side Entry with Safety Outlet Covers					
04674	2.5	White	Blister	12	10.5
6 Outlet Strip with Longer Cord					
05658	15	White	Box	12	26
6 Outlet Metal Strip					
04618	4	Black	Box	20	39.2
8 Outlet Power Center					
04613	6	Ivory	Box	6	10.5

COLEMAN CABLE

Adapters



Mfg Part#	Color	Package	Master Pk Qty	Master Pk Wt
3 Outlet Adapter with Auto-on Nightlight				
04629	White	Blister Card	24	6
3 Outlet Adapter				
04659	White	Blister Card	24	4.5
6 Outlet Adapter				
04660	White	Blister Card	24	8.4
6 Outlet Adapter				
04614	Ivory	Blister Card	24	9.2
6 Outlet Side Entry Adapter				
04670	White	Blister Card	12	7.7

COLEMAN CABLE

Booster Cable Clamps
Accessories

Mfg Part#	Desc.	Master Pk Qty	Master Pk Wt
965	Batt. Terminal Lifter	6	3
969	Batt. Ter. Cap Protector	6	1
970	Rubber Battery Filter	6	3
971	4 way battery Tool	6	3
985	Top Post Battery Carrier	6	2
986	Battery Post & Ter. Cleaner	6	1
989	Top or Side Post	12	1
991	Mini Batt. Tester	6	1
992	Hydrometer	4	2
993	Hydrometer	4	2
994	Side Ter. Wrench	4	1
995	Batt. Filler Bottle	6	3

Copper Lugs

1809	4 & 6 Gauge	25	1
1809-2	4 & 6 Gauge	24	2
1810	2 Gauge Bulk	25	1
1810-2	2 Gauge Bulk	24	2
1811	1 Gauge	25	2
1812	0 Gauge	25	2

COLEMAN CABLE

Booster Cables
400 Amp Polar-Glo™ Clamps
Road Power®



Featuring glow-in-the-dark polarity indicators. The Polar-Glo™ clamp is ergonomically designed to be handled easily by everyone. This clamp grips remarkably to both top and side post batteries, both firmly and easily. The extended jaw has grooves, which conform to the side post, locking it in place. The Polar-Glo™ clamp is the perfect solution to the problem of jumping side post batteries.

Mfg Part#	Wire Gauge	Color	Length	Master Pk Qty	Master Pk Wt
08465	8	Yellow	12	6	24
08466	8	Yellow	16	6	27
08467	8	Yellow	12	2	8
08471	8	Yellow	12	6	22
08565	6	Orange	12	6	25
08566	6	Orange	16	6	30
08568	6	Orange	16	4	21
08665	4	Red	12	6	33
08666	4	Red	16	6	41
08660	4	Red	20	2	16
08662	4	Red	25	2	20

COLEMAN CABLE

Booster Cables
500 Amp Parrot Jaw Clamps
Road Power®
With Welding Cable Construction



Mfg Part#	Wire Gauge	Color	Length	Master Pk Qty	Master Pk Wt
08765	4	Black	12	2	13
08766	4	Black	16	2	16
08760	4	Black	20	2	18
08860	2	Black	20	2	24
08862	2	Black	25	2	29

COLEMAN CABLE

Booster Cables
200 Amp Polar-Glo™ Clamps
Road Power®



Our top selling quality cable insulation. Featuring No-Tangle construction with flexible wire stranding and heavy-duty copper-plated steel clamps.

Mfg Part#	Wire Gauge	Color	Length	Master Pk Qty	Master Pk Wt
08120	10	Black	12	6	18
08435	8	Yellow	12	6	17
08445	8	Yellow	12	4	14

COLEMAN CABLE

Booster Cable Clamps
Road Power®



Rugged color-coded replacement clamps.

Mfg Part#	Clamp Rating	Master Pk Qty	Master Pk Wt
-----------	--------------	---------------	--------------

Copper Plated Steel

150C-2	150 Amp	6	3
75C-2	75 Amp	6	1
50C-10	50 Amp	10	5

Vinyl Coated Steel

400C-2	400 Amp	6	6
08903	500 Amp	12	10
08904	500 Amp	12	13

COLEMAN CABLE

RV/Mobile Home Cords
Accessories



Mfg Part#	Cord Length	Desc.	Male	Female	Master Pk
-----------	-------------	-------	------	--------	-----------

RV Adapters & Accessories

09521	-	Adapter	5-15P	30A RV	100
09522	-	Adapter	30A RV	5-15R	100
09524	-	Right Angle Adapter	5-15P	30A RV	100
09523	-	Replacement Plug	30A RV Plug	-	-

Mfg Part#	Cord Length	Desc.	Male	Female	Master Pk
09543	-	Replacement Plug	50A RV Plug	-	-

Adapter Extension Cord Sets

09548	9"	14/3 STW	5-15P	30A RV Straight	50
09542	18"	14/3 STW	5-15P	30A RV	12
09544	18"	14/3 STW	30A RV	5-15R	12
09552	18"	10/3 STW	30A RV	50A 14-50R	50
09554	18"	10/3 STW	50A 14-50P	30A RV	50
09553	12"	10/3 STW Twist to Lock	30A L5-30P	30A RV	50
09538	18"	10/3 STW	30A RV	50A Marine w/Boot	-
09539	25'	10/3 STW	30A RV	50A Marine w/Boot	5

30A & 50A RV Power Supply Cords

09575	18"	10/3 STW	30A RV	-	50
09572	18"	10/3 STW	-	30A RV	50
09525	25'	10/3 STW	30A RV	-	10
09529	28'	10/3 STW	30A RV	-	10
09519	30'	10/3 STW	30A RV	-	8
09532	32'	10/3 STW	30A RV	-	8
09535	35'	10/3 STW	30A RV	-	8
09516	36'	10/3 STW	30A RV	-	8
09541	40'	10/3 STW	30A RV	-	6
09546	42'	10/3 STW	30A RV	-	6
09531	50'	10/3 STW	30A RV	-	5
09547	17"	6/3 & 8/1 STW	50A 14-50P	-	25
09549	17"	6/3 & 8/1 STW	-	50A 14-50P	25
09527	25'	6/3 & 8/1 STW	50A 14-50P	-	3
09528	28'	6/3 & 8/1 STW	50A 14-50P	-	3
09530	30'	6/3 & 8/1 STW	50A 14-50P	-	3
09536	36'	6/3 & 8/1 STW	50A 14-50P	-	3
09560	25'	6/3 & 8/11 Flexible SEW 90C	50A 14-50P	-	3
09564	28'	6/3 & 8/11 Flexible SEW 90C	50A 14-50P	-	3
09562	30'	6/3 & 8/11 Flexible SEW 90C	50A 14-50P	-	3
09561	36'	6/3 & 8/11 Flexible SEW 90C	50A 14-50P	-	3
09537	40'	6/3 & 8/11 Flexible SEW 90C	50A 14-50P	-	3

15A, 30A & 50 RV Extension Cord Sets

09506	25'	14/3 STW	5-15P	5-15R	12
09526	30'	14/3 STW	5-15P	5-15R	-
09507	25'	14/3 ST	15A/125V	-	-
09517	25'	10/3 ST	30A/125V	-	-
09510	10'	10/3 STW	30A RV	30A RV	20
09550	25'	10/3 STW	30A RV	30A RV	10
09555	50'	10/3 STW	30A RV	30A RV	5
09570	30'	10/3 STW	30 RV	30 RV	-
09590	25'	6/3 & 8/1 SEW	50A 14-50R	50A 14-50R	2

COLEMAN CABLE

Primary Wire

Road Power®

Engineered to handle the harsh environment of an automobile engine, the durable PVC outer-jacket resists water, oil, chemicals, and abrasion.



Mfg Part#	Wire Gauge	Color	Length	Master Pk Qty	Master Pk Wt
10-1	10	Assort. Colors	7	6	2
10-1-11	10	Black	7	6	2
10-1-12	10	Blue	7	6	2
10-1-14	10	Yellow	7	6	2
10-1-15	10	Green	7	6	2
10-1-16	10	Red	7	6	2
10-1-17	10	White	7	6	2
12-1	12	Assort. Colors	11	6	2
12-1-11	12	Black	11	6	2
12-1-12	12	Blue	11	6	2
12-1-14	12	Yellow	11	6	2
12-1-15	12	Green	11	6	2
12-1-16	12	Red	11	6	2
12-1-17	12	White	11	6	2
14-1	14	Assort. Colors	17	6	2
14-1-11	14	Black	17	6	2
14-1-12	14	Blue	17	6	2
14-1-14	14	Yellow	17	6	2
14-1-15	14	Green	17	6	2
14-1-16	14	Red	17	6	2
14-1-17	14	White	17	6	2
16-1	16	Assort. Colors	24	6	2
16-1-11	16	Black	24	6	2
16-1-12	16	Blue	24	6	2
16-1-14	16	Yellow	24	6	2
16-1-15	16	Green	24	6	2
16-1-16	16	Red	24	6	2
16-1-17	16	White	24	6	2
18-1	18	Assort. Colors	24	6	2
18-1-11	18	Black	24	6	2
18-1-12	18	Blue	24	6	2
18-1-14	18	Yellow	24	6	2
18-1-15	18	Green	24	6	2
18-1-16	18	Red	24	6	2
18-1-17	18	White	24	6	2