

HG 2320 ESD

Electrostatic Discharge Heat Gun

Technical Specifications

Voltage:	120 VAC / 60 Hz
Power:	1600 watts
Amps:	13.3
Surface Conductivity:	10 ⁴ ohms
Airflow Rate:	4-13 cfm. (continuously variable)
Stages:	2 (continuously variable)
Power Cord:	Industrial grade rubber, length: 6 ft
Motor:	Brush motor
Heating Element:	Ceramic heating element
Motor Lifetime:	1000 hours
Accessories:	Use of standard accessories
Temperature:	120-1200 ° F
Net Weight:	2.19 lbs
Dimensions:	9.96" x 3.41" x 7.87"
(L x W x D)	
Single Sell Pack:	Dimensions: 10.20" x 3.54" x 9.33" Weight: 2.60 lbs
Features:	Higher durability (+20%), optimized weight balance, LCD-Display, 4 settings programmable, heat build-up warning, hanging ring, easily replaceable power cord, residual heat indicator, optional temperature scanner and fine dist filter
Warranty:	1 year



UPC Code	Product No.
0 18139 73503 8	110073503