



7W

VT-707 7W LED WALL LIGHT COLORCODE:3000K IP65 BLACK BODY

Lumens <b>770</b>	Beam Angle <b>360</b>	Dimensions <b>110x120x170mm</b>
----------------------	--------------------------	------------------------------------

Warm White  
 SKU:8219

**2** YEARS  
 WARRANTY

**SENSOR**  
 COMPATIBLE



## Technical Information

Instant Start: 0-100% in 1/1s	Dimmable: No
Watts: 7	Warranty (Years): 2
Lumens: 770	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: Black	Operation Temperature: -25 to +50°C
Body Type: Aluminium	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
IP Rating: IP65	

## Features

- ✓ Perfect choice for in-line lighting with Architectural structures
- ✓ 4 way wall washer to create blade lighting effects
- ✓ Create your light show in facades, corridors, stage shows etc
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Reflective PMMA Screen for 360 degree light ray transmission
- ✓ IP65 rated solid ingress protection
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.921
Length(Box)mm	160
Width(Box)mm	130
Height(Box)mm	130
Unit CBM	0.002704

### Listing Details

EAN Code	3800157623360
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	300

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES