



6W

VT-806 6W LED WALL LAMP COLORCODE:4000K WHITE

Lumens 480	Beam Angle 100	Dimensions 100x93mm
----------------------	--------------------------	-------------------------------

Day White
 SKU:8252

3 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP20
Watts:	6	Dimmable:	No
Lumens:	480	Warranty (Years):	3
Beam Angle:	100	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Plastic + Metal	Operation Temperature:	-20 to +45°C
Long life:	30,000 Hours	Input Power:	AC 220-240V, 50/60Hz
LED Chip Type:	SMD	Sensor Compatibility:	Yes

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note: 24H*

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.388
Length(Box)mm	110
Width(Box)mm	110
Height(Box)mm	110
Unit CBM	0.001331

Listing Details

EAN Code	3800157627023
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	24
Qty Per Pallet	840

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES