


Tektronix TBS2000B

Digital Storage Oscilloscope, Up to 200MHz & 2GS/s

- Capture More
- See More
- Find More
- Analyze More
- Access More
- Learn More




Draft Images

	TBS2072B TBS2074B	TBS2102B TBS2104B	TBS2202B TBS2204B
Bandwidth	70MHz	100MHz	200MHz
Analog Channels	2 or 4		
Sample Rate	1GS/s (All) - 2GS/s (Half)		
Record Length	5M Points		
Vertical Resolution	8 Bit		
Probe Interface	TekVPI with support for passive BNC probes, Active Voltage, Current and Power probes		
Trigger	Edge, Pulse Width, Runt		
Analysis	34 Automated Measurements, Math, Ref, Cursors, FFT, Search and Mark, Zoom, Autoset		
Display Size	9in WVGA		
I/O	USB Host, USB Device, LAN, Aux Out, WiFi (Optional)		
Security	Kensington Lock		
Software	Courseware, Tek SmartLab, OpenChoice, TekBench, Kickstart		
Warranty	5 Year		
Price Range	\$1,370 - \$3,030		

Field Upgradable Bandwidths For All Models Lower Noise Front End Design



TBS2000B




TBS2000



Enhanced Search & Mark



Disable Measurements



Automatic Measurements – Measure with Confidence



Protocol Decode and Trigger coming up mid-2020 ... Stay Tuned!

Please refer to www.tek.com/oscilloscope/tbs2000-basic-oscilloscope for more details