



TECHNICAL DATA SHEET

PRO-ELEC

Cable Glands - Spiral CB21922 - 945

**RoHS
Compliant**

Thread D1	Cable Range	H (mm)	GL (mm)	D (mm)	Spanner Size (mm)	Part Number	
						Black	Grey
M12x1.5	3-6.5	54	8	7	15	CB21922	CB21923
M16x1.5	4-8	63	8	8.5	19	CB21924	CB21925
M16x1.5	5-10	78	8	10.5	22	CB21926	CB21927
M20x1.5	6-12	8-12	9	13	24	CB21928	CB21929
M20x1.5	10-14	11-14	9	15.5	27	CB21930	CB21931
M25x1.5	13-18	14-18	11	20	33	CB21932	CB21933
PG7	3-6.5	18-25	8	7	15	CB21934	CB21935
PG9	4-8	4-7	8	8.5	19	CB21936	CB21937
PG11	5-10	5-8	8	10.5	22	CB21938	CB21939
PG13.5	6-12	8-12	9	13	24	CB21940	CB21941
PG16	10-14	11-14	10	15.5	27	CB21942	CB21943
PG21	13-18	16-22	11	20	33	CB21944	CB21945
Material (A,C,E):		PA (Nylon)					
Material (B,D):		NBR					
Protection Degree:		IP68					
Working Temperature		-20 to 80°C					



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC