



**50" Full HD LED Digital TV with Built-in Freeview T2 HD**

- 50" Full HD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- 3 x HDMI inputs for your external devices and consoles
- Can be wall mounted (400mm x 400mm)

	<b>EAN</b>	<b>5060062269673</b>
<b>Specifications</b>	Model No.	C5020DVB
	Chipset	MSD3663
	Sales Market	England
	VESA Size	400 x 400
	Wall Mount Screws	M6 x 8
	Speaker Output	2 x 8w
	Actual Size of Display (Diagonal)	50"

<b>Display</b>	Display Type	LED
	Resolution	1920 x 1080 (16:9)
	Brightness (nit)	220
	Contrast	4000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Response Time	6.5ms

<b>Terminals</b>	HDMI Input	3
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Output	1
	15-PIN VGA + AUDIO Input	1
	RF Input	1
	Optical Digital AUDIO Output	1
	Coaxial Digital AUDIO Output	0
	Analog AUDIO Output	0
	3.5mm Headphone Output	1

<b>Accessories</b>	Remote	1
	Battery	AAA x 2
	User Manual	English

<b>Other Features</b>	DVD Player	No
	DVB-S	Without
	DVB-S2	Without
	DVB-T	With
	DVB-T2	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/ Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

<b>Power</b>	Power Supply	AC 120V-230V, 50Hz/60Hz
	Power Consumption	130W
	Standby Power Consumption	<0.5W

<b>Dimension</b>	Unit Dimension With Stand (W x D x H mm)	
	Unit Dimension Without Stand (W x D x H mm)	
	Weight of unit (kg)	