



55" 4K Ultra HD LED Smart TV with Wi-Fi and Freeview T2 HD

- 55" 4K Ultra HD widescreen LED TV
- Pre-loaded with popular catch up and streaming apps
- Built in Wi-Fi
- T2 HD channels
- 3840 x 2160 screen resolution
- USB - record digital TV and play media files from other devices
- HDMI x 3 inputs for xternal devices & consoles
- Can be wall mounted (400mm x 200mm bracket not included)

	EAN	5060062269895
Specifications	Model No.	C5520RTS4K
	Chipset	2861
	Sales Market	England
	VESA Size	400 x 200
	Wall Mount Screws	M6
	Speaker Output	2 x 8w
	Actual Size of Display (Diagonal)	55"

Display	Display Type	LED
	Resolution	3840 x 2160
	Brightness (nit)	200
	Contrast	3500:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Response Time	8ms

Terminals	HDMI Input	3
		480i, 480p, 576i, 576p, 720p, 1080i, 1080p, 4k
	RJ45	1
	EARPHONE	1
	15-PIN VGA + AUDIO Input	1
	MINI Component + AUDIO Input	1
	MINI Composite + AUDIO Input	1
	Optical Digital AUDIO Output	1
	RF Input	1

Accessories	Remote	1
	Battery	AAA x 2
	User Manual	English

Other Features	SMART (Android)	Yes
	DVB-S	Without
	DVB-S2	Without
	DVB-T	With
	DVB-T2	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/ Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift
EPG recording reservation		

Power	Power Supply	AC 120V-230V, 50Hz/60Hz
	Power Consumption	150W
	Standby Power Consumption	<1W

Dimension	Unit Dimension With Stand (W x D x H mm)	1250 x 270 x 784
	Unit Dimension Without Stand (W x D x H mm)	1250 x 87 x 729
	Weight of unit (kg)	