

CTX30 Tone and Probe Kit

Quickly trace various types of unenergized cable including electrical wire, twisted pair, LAN, multi-conductor, telephone, alarm and others

Features:

- Insulated probe tip prevents short circuits
- Adjustable sensitivity
- Audible and visual notification
- Tip/Ring/Continuity testing
- RJ11 and Alligator clip connectors

Applications:

- Trace various types of unenergized cable including electrical wire, twisted pair, LAN, multi-conductor, telephone, alarm and others



	CTX30
Input Voltage/Current	Max: 24VAC, 42VDC, 15A
Resistance	Max: 10k Ω (for continuity testing)
Power	9V Batteries for Toner and Probe (not included)
Dimensions	Toner: 2.63 x 2.75 x 1.12" (66.8 x 69.8 x 28.4mm) Probe: 8.5 x 2 x 1.4" (216 x 51 x 36mm)
Weight	Toner: 3.2oz (91g) Probe: 3.2oz (91g)

Ordering Information:

CTX30 Tone and Probe Kit