

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150200212](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 20 Circuits, 0.102m Cable Length, Gold (Au) Plating

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-15020-001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)
[Packaging Specification PK-15020-001-001 \(PDF\)](#)

General

Product Family [Cable](#)
Series [15020](#)
Comments [Contacts on opposite sides, Type D, Contacts on opposite sides, Type D](#)
Crimp Quality Equipment [Yes](#)
Overview [Premo-Flex Cable Jumpers](#)
Product Name [Premo-Flex FFC Jumper](#)
UPC [884982176744](#)

Physical

Cable Length [0.102m](#)
Circuits (Loaded) [20](#)
Circuits (maximum) [20](#)
Net Weight [0.675/g](#)
Packaging Type [Bag](#)
Pitch - Mating Interface [0.50mm](#)
Temperature Range - Operating [-40° to +105°C](#)
Wire Size AWG [N/A](#)
Wire/Cable Type [Flat Flex Cable](#)

Electrical

Current - Maximum per Contact [0.5A](#)
Voltage - Maximum [60V AC](#)

Material Info

Reference - Drawing Numbers

Packaging Specification [PK-15020-001-001](#)
Product Specification [PS-15020-001-001](#)
Sales Drawing [SD-15020-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15020 Series](#)

Mates With

Easy-On FFC/FPC Connector:

[5034802000](#) , [5051102091](#) , [5051102096](#)
, [527452097](#) , [527462071](#) , [5019512010](#) ,
[5019512030](#) , [5019512050](#) , [525592052](#)