

Fuse - FUSE-10X38-16A-GR - 2903126


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 16 A, tripping characteristic: super-fast blow (gR)



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 713313
GTIN	4046356713313
Weight per Piece (excluding packing)	8.050 g
Custom tariff number	85361050
Country of origin	France
Note	Made to Order (non-returnable)

Technical data

General

Number of fuses in the set	10
Nominal voltage U_N	690 V
Nominal current I_N	16 A
Fuse	Fuse
Tripping characteristic	super-fast blow (gR)
Fuse rating	CC
Dimensions	10 x 38 mm

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Fuse - FUSE-10X38-16A-GR - 2903126

Classifications

eCl@ss

eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142002
eCl@ss 8.0	27142002
eCl@ss 9.0	27142002

ETIM

ETIM 3.0	EC000035
ETIM 4.0	EC002704
ETIM 5.0	EC002704
ETIM 6.0	EC002704
ETIM 7.0	EC002704

UNSPSC

UNSPSC 6.01	30211915
UNSPSC 7.0901	39121514
UNSPSC 11	39121514
UNSPSC 12.01	39121514
UNSPSC 13.2	39121627
UNSPSC 18.0	39121627
UNSPSC 19.0	39121627
UNSPSC 20.0	39121627
UNSPSC 21.0	39121627

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Fuse - FUSE-10X38-16A-GR - 2903126

Approvals

EAC



RU C-
DE.A*30.B.01082