

Mounting material - PSD-S ME OB/MB - 2700155

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Outlet box with magnetic base for base mounting, black

Your advantages

- Magnetic base for tool-free mounting on metal surfaces
- With concealed cable routing

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491464
GTIN	4046356491464
Weight per Piece (excluding packing)	303.900 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Diameter	70 mm
Height	45.5 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

General

Material	PA-GF
Color	black
Weight	299 g
Mounting position	any

Mounting material - PSD-S ME OB/MB - 2700155

Technical data

General

Mounting type	Base mounting
	Tube mounting
Assembly instructions	Magnetic holder
Scope of delivery	2 x plastic screw 1 x cable threaded joint 1 x nut 1 x seal

Connection data


Connection method	Screw connection
-------------------	------------------

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27143200
eCl@ss 4.1	27143200
eCl@ss 5.0	27371200
eCl@ss 5.1	27371200
eCl@ss 6.0	27371200
eCl@ss 7.0	27371232

Mounting material - PSD-S ME OB/MB - 2700155

Classifications

eCl@ss

eCl@ss 8.0	27371232
eCl@ss 9.0	27371232

ETIM

ETIM 3.0	EC001152
ETIM 4.0	EC001152
ETIM 5.0	EC001152
ETIM 6.0	EC001152
ETIM 7.0	EC001152

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311
UNSPSC 18.0	46171604
UNSPSC 19.0	46171604
UNSPSC 20.0	46171604
UNSPSC 21.0	46171604

Approvals


Approvals


Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU *- DE.A*30.B.00237
-----	---	--------------------------

