

# Transition sleeve from hose to cable - WP-EC TPE HF 42,5 BK - 3240980


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves, transition sleeves, from hose to cable



## Key Commercial Data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 710985
GTIN	4046356710985
Weight per Piece (excluding packing)	14.250 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

## Technical data

### Dimensions

Length (b)	46 mm
Diameter	42.5 mm
Outside diameter	42.5 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Short-term temperature	150 °C

### General

Color	black
Components	halogen-free
Flammability rating according to UL 94	HB

# Transition sleeve from hose to cable - WP-EC TPE HF 42,5 BK - 3240980

## Technical data

### General

Material	TPE
----------	-----

### Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27430316
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439210
eCl@ss 8.0	27439210
eCl@ss 9.0	27430316

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519
ETIM 6.0	EC000519
ETIM 7.0	EC000519

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121404
UNSPSC 18.0	39121404
UNSPSC 19.0	39121404
UNSPSC 20.0	39121404
UNSPSC 21.0	39121404

# Transition sleeve from hose to cable - WP-EC TPE HF 42,5 BK - 3240980

## Approvals

### Approvals

---

#### Approvals


UL Recognized

---

#### Ex Approvals

---

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
---------------	-----------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------

---