

Flange cover - UWV 25-F - 3074622


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flange, number of positions: 0, color: gray



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 421850
GTIN	4046356421850
Weight per Piece (excluding packing)	8.700 g
Custom tariff number	85472000
Country of origin	China
Note	Made to Order (non-returnable)

Technical data

Item properties

Number of positions	0
---------------------	---

Dimensions for the product

Pitch	0 mm
-------	------

Packaging information

Pieces per package	10
Denomination packing units	Pcs.

Standards and Regulations

Connection in acc. with standard	UL
----------------------------------	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

Flange cover - UWV 25-F - 3074622

Technical data

Environmental Product Compliance

	No hazardous substances above threshold values
--	--

Classifications

eCl@ss

eCl@ss 4.0	21011300
eCl@ss 4.1	21011300
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133
eCl@ss 9.0	27141133

ETIM

ETIM 2.0	EC001283
ETIM 3.0	EC001283
ETIM 4.0	EC000886
ETIM 5.0	EC000886
ETIM 6.0	EC000886
ETIM 7.0	EC000886

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121425
UNSPSC 18.0	39121425
UNSPSC 19.0	39121425
UNSPSC 20.0	39121425
UNSPSC 21.0	39121425

Approvals

Approvals

Approvals

EAC

Flange cover - UWV 25-F - 3074622

Approvals

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

