


# Front plate - SI-FP-R1A-U1A/0,7 - 1404512

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Front plate with contact inserts, plastic with shroud, 1 x USB (socket/socket/0.7 m cable) type A; 1 x RJ45, 8-pos. metal, CAT5e (socket/socket)



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 698528
GTIN	4046356698528
Weight per Piece (excluding packing)	76.400 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

### Mechanical characteristics

Degree of protection	IP20
Contact insert design	with 1x RJ45 Socket/socket, snap-in slot locking
	with 1x USB A 2.0 Socket/socket with 0.7 m cable, snap-in slot locking

### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

### Material data

Material	PBT (Front plate)
Depth	20 mm
Height	29.7 mm

### Electrical characteristics

Rated current	1 A ()
---------------	--------

### Environmental Product Compliance

	Lead 7439-92-1
--	----------------

# Front plate - SI-FP-R1A-U1A/0,7 - 1404512


## Technical data

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 4.0	27140800
eCl@ss 4.1	27140800
eCl@ss 5.0	27189200
eCl@ss 5.1	27189200
eCl@ss 6.0	27189200
eCl@ss 7.0	27189217
eCl@ss 8.0	27189217
eCl@ss 9.0	27189217

### ETIM

ETIM 3.0	EC000007
ETIM 4.0	EC001855
ETIM 5.0	EC000456
ETIM 6.0	EC000456

# Front plate - SI-FP-R1A-U1A/0,7 - 1404512

## Classifications

### ETIM

ETIM 7.0	EC000456
----------	----------

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121302
UNSPSC 18.0	39121302
UNSPSC 19.0	39121302
UNSPSC 20.0	39121302
UNSPSC 21.0	39121302

## Approvals

### Approvals




Approvals

EAC / EAC



Ex Approvals



### Approval details

EAC		EAC-Zulassung
-----	--	---------------

EAC		RU C- DE.A*30.B.01102
-----	--	--------------------------

## Accessories

Accessories

Device marking

## Front plate - SI-FP-R1A-U1A/0,7 - 1404512

### Accessories

Snap-in markers - UCT-EM (20X7) - 0801494



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 20 x 7 mm, Number of individual labels: 24

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>