

## Front plate - VS-SI-FP-2RJ45-5-MOD-BU/BU - 1657766


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Front plate with contact inserts, plastic with shroud, 2x RJ socket/socket

RoHS

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 118705
GTIN	4046356118705
Weight per Piece (excluding packing)	44.010 g
Custom tariff number	85366990
Country of origin	Taiwan

### Technical data

#### Mechanical characteristics

Number of slots	2
Color	gray
Degree of protection	IP20

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

#### Material data

Flammability rating according to UL 94	V0
Material	PBT (Front plate)
Height	45 mm

#### Electrical characteristics

Rated voltage (III/3)	50 V
Rated current	1 A

#### Standards and Regulations

# Front plate - VS-SI-FP-2RJ45-5-MOD-BU/BU - 1657766

## Technical data

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


## Drawings

Schematic diagram



# Front plate - VS-SI-FP-2RJ45-5-MOD-BU/BU - 1657766

Dimensional drawing



Dimensional drawing

## Classifications

### eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27144000
eCl@ss 5.1	27144000
eCl@ss 6.0	27144000
eCl@ss 7.0	27144001
eCl@ss 8.0	27189217
eCl@ss 9.0	27189217

### ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007

# Front plate - VS-SI-FP-2RJ45-5-MOD-BU/BU - 1657766

## Classifications

### ETIM

ETIM 4.0	EC000007
ETIM 5.0	EC000456
ETIM 6.0	EC000456
ETIM 7.0	EC000456

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	39121302
UNSPSC 19.0	39121302
UNSPSC 20.0	39121302
UNSPSC 21.0	39121302

## Accessories

### Accessories

### Device marking

Snap-in markers - UCT-EM (20X7) - 0801494



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 20 x 7 mm, Number of individual labels: 24

### Marking material

Marker labels - VS-SI-BZ - 1656660



Marker label, plastic, plate with 20 labels