


Socket insert - VS-SI-SD-USA - 1656521

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Ground contact socket, plastic, for USA



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 029896
GTIN	4046356029896
Weight per Piece (excluding packing)	78.400 g
Custom tariff number	85366990
Country of origin	Hungary

Technical data

Mechanical characteristics

Connection method	Slip-on connection
Conductor cross section	2.5 mm ²
Weight	78.4 g

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Degree of protection	IP20

Material data

Housing material	PA
Assembly instructions	suitable for all mounting frames

Electrical characteristics

Connection cross section AWG	14
Rated current	15 A

Standards and Regulations

Socket insert - VS-SI-SD-USA - 1656521

Technical data

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Socket insert

Socket insert - VS-SI-SD-USA - 1656521

Classifications

eCl@ss

eCl@ss 4.0	27142300
eCl@ss 4.1	27142300
eCl@ss 5.0	27142300
eCl@ss 5.1	27142300
eCl@ss 6.0	27142300
eCl@ss 7.0	27142305
eCl@ss 8.0	27142305
eCl@ss 9.0	27142305

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC000125
ETIM 4.0	EC000125
ETIM 5.0	EC001663
ETIM 6.0	EC001663
ETIM 7.0	EC001663

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121406
UNSPSC 18.0	39121406
UNSPSC 19.0	39121406
UNSPSC 20.0	39121406
UNSPSC 21.0	39121406

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

Socket insert - VS-SI-SD-USA - 1656521

Approvals

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU C- DE.A*30.B.01102
-----	---	--------------------------