

PRODUCT-DETAILS

## CUE 416-6+R/BS13

Surface socket-outlet, 6h, 16A, IP44, 3P+N+E and 2-pole British standard outlet.



### General Information

Extended Product Type	CUE 416-6+R/BS13
Product ID	2CMA101635R1000
EAN	7392696016353
Catalog Description	Surface socket-outlet, 6h, 16A, IP44, 3P+N+E and 2-pole British standard outlet.
Long Description	Wall mounted socket IEC and 2 pole British outlet, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

### Ordering

EAN	7392696016353
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	10 piece

### Dimensions

Product Net Width	82 mm
Product Net Height	110 mm
Product Net Length	160 mm
Product Net Depth / Length	160 mm

Product Net Weight	0.38 kg
--------------------	---------

### Container Information

Package Level 1 Width	162 mm
Package Level 1 Depth / Length	162 mm
Package Level 1 Height	112 mm
Package Level 1 Gross Weight	3.8 kg
Package Level 1 EAN	7392696016384
Package Level 1 Units	box 10 piece
Package Level 2 Units	40 piece

### Technical UL/CSA

Tightening Torque UL/CSA	7.1 in·lb
-----------------------------	-----------

### Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0003
Declaration	2CMC700005D0003
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1618716
REACH Declaration	2CMC700005D0003

### Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm <sup>2</sup>
Cable Entry Position	Swivel
Color	Red
Connection Type	Screw Clamp
Degree of Protection	IP44
Frequency (f)	50 Hz 60 Hz
Function	Wall mounted IEC socket with domestic socket
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P-S#CUE 416-6+R/BS13
Material	Plastic
Mounting Holes	120x72
Number of Poles	5
Order Multiple	10 piece
Product Main Type	CUE

Product Name	Wall mounted IEC socket with domestic socket
Protection Type	Splashproof
Rated Current ( $I_n$ )	16 A
Rated Frequency (f)	50...60 Hz
Rated Voltage ( $U_r$ )	200/346 ... 240/415 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC000050M0001
Installation Manual	2CMC000050M0001
RAL Number	RAL 7001 - Silver Grey

---

## Classifications

eClass	27440504
UNSPSC	39120000

---

## Technical

Wire Size	14 ... 12 AWG
Tightening Torque	0.8 N·m

---

## Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Special Plugs & Sockets → Appliances

