

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2119370002](#)
Status: **Active**
Overview: Coeur CST High-Current Interconnect System
Description: Coeur CST High-Current Male Header, Dual Row, 2 Circuits, 6.00mm Diameter, Screw Attach, Keying Option A, Red

Documents:

Drawing (PDF)	Test Summary 2119410000-TS-000 (PDF)
Product Specification 2119410000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2119410000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	PCB Headers
Series	211937
Application	Power, Wire-to-Board
Overview	Coeur CST High-Current Interconnect System
Product Name	Coeur CST
UPC	193264140541

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Diameter	6.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Material - Resin	Polyester
Net Weight	42.935/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
Pitch - Mating Interface	19.06mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Screw

Electrical

Current - Maximum per Contact	120.0A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Application Specification	2119410000-AS-000
Product Specification	2119410000-PS-000
Sales Drawing	2119370000-SD-000
Test Summary	2119410000-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[211937](#) Series

Mates With

6.00mm Receptacle Crimp Housing [211942](#)