

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0369220305](#)  
**Status:** **Active**  
**Overview:** [Ditto Wire-to-Wire Interconnects](#)  
**Description:** Ditto-to-Ditto Off-the-Shelf (OTS) Cable Assembly, 3.00mm Pitch, Single Row, 450.00mm Length, 3 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">36922</a>
Application	Power, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Ditto-to-Ditto
Overview	<a href="#">Ditto Wire-to-Wire Interconnects</a>
Product Name	Ditto
Type	Discrete Wire Assembly
UPC	193264208845

**Physical**

Cable Length	450.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Hermaphroditic-Hermaphroditic
Lock to Mating Part	Yes
Material - Metal	Tin Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	14.960/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.35-1.70mm
Wire Size AWG	20
Wire/Cable Type	UL 1061


**Electrical**

Current - Maximum per Contact	4.8A
Voltage - Maximum	350V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	369220300-000
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[36922 Series](#)

**Mates With**

Ditto Hermaphroditic Crimp Housing [150170](#)

**Use With**

Ditto Hermaphroditic Terminals [150200](#)

<br>Ditto TPA Retainer [150212](#)