

Utility Hand Tools

Klein® manufactures the highest quality tools in the industry, supporting linemen and utility workers around the world with premium products—quality and reliability you can count on every day.



KLEIN TOOLS®
EST. 1857
TOOLS

For Professionals... Since 1857®

Open Jaw Cable Cutter

- High-leverage ratchet mechanism for single-handed cutting of copper and aluminum without burrs or sharp edges.
- Front loading jaws for tight applications.
- Spring release lever allows for fast jaw reset in between cuts.
- Plastic covered handles with hand guards for comfort and firm grip.
- One-year warranty.

Cat. No.	Max. Cable Cutting Capacity	Overall Length	Weight
63711	600 MCM (300 mm ²) Copper and 750 MCM (400 mm ²) Aluminum 1-1/8" Communication cable	11.5" (292.1 mm)	2.0 lbs. (0.91 kg)

⚠WARNING: Do NOT use to cut steel or ACSR.

Capacity



63711



3-in-1 Impact Socket – Distribution | Transmission

- NRHD Distribution socket features three square socket sizes: 3/4", 1", and 1-1/8".
- NRHD2 Transmission socket features three square socket sizes: 1-1/8", 1-5/16", and 1-1/2".
- 7/16" hex quick-change adapter included.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- Long hollow shaft allows use on long threaded bolts.

Cat. No.	Overall Length	Weight
NRHD	7 3/4" (196.9 mm)	2.0 lbs. (0.91 kg)
NRHD2	11" (279.4 mm)	3.25 lbs. (1.47 kg)



NRHDA



NRHDA2

Impact Socket Adapters

- Impact socket adapter.
- 7/16" hex quick-change adapter.
- Fine-tuned ball detent provides improved retention, minimizing drops.
- Do not exceed 200 ft. lbs of torque.

Cat. No.	Description	Hex Size
NRHDA	Distribution Socket Adapter	7/16"
NHRDA2	Transmission Socket Adapter	7/16"



NRHD

NRHD2

Klein-Kurve® Skinning Knife

- 2" blade for increased control when scoring and slitting cable jacket.
- Ergonomic handle for maximum comfort.
- Oversized ring for strength and easy storage.
- Notch on blade back for scraping or removing wire insulation.




1580-3

Cat. No.	Overall Length	Weight
1580-3	8-3/4" (222.3 mm)	0.28 lbs. (0.13 kg)



25" Standard Cable Cutter

- Replaceable hook-jaw blades grab and hold cable while shear-cutting action makes clean cuts.
- Fiberglass handles with heavy vinyl grips for comfort and slip resistance.
- Jaws are forged tool steel with black-oxide finish for long life.
- Minimal blade friction allows handle to be opened using only gravity.
- Make a clean, even cut for ease in fitting lugs and terminals.
- Not designed for cutting steel or ACSR.
- Includes rubber sleeves.



Rollpin prevents snags



63041TH


Cat. No.	Soft Cable Capacity	MCM Cable Capacity	Overall Length	Weight
63041TH	1-3/8" (35 mm)	Copper: 500 Aluminum: 750	25 -1/2" (648 mm)	5.25 lbs. (2.38 kg)

▲WARNING: Do NOT use to cut steel or ACSR.



Pole Punch

- Ergonomic handle with overstrike protection.
- Thermoplastic handle withstands harsh conditions and is resistant to oil and grease.
- Large strike plate transfers force directly into the hardware, reducing vibration.
- Chamfered tip assists centering and reduces drag.



Cat. No.	Overall Length	Weight
66326	18" (457.2 mm)	1.03 lbs. (0.47 kg)

66326

