

## Han 55DDD F-c



Image is for illustration purposes only. Please refer to product description.

Part number	09 16 055 2101
Specification	Han 55DDD F-c
HARTING eCatalogue	<a href="https://b2b.harting.com/09160552101">https://b2b.harting.com/09160552101</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> DDD

### Version

Termination method	Crimp termination
Gender	Female
Size	6 B
Number of contacts	55
PE contact	Yes
Details	PE connection with a Han D <sup>®</sup> crimp contact Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

## Specifications and approvals

Specifications	IEC 61984
----------------	-----------

## Commercial data

Packaging size	1
Net weight	1 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors