

Han 75DDD F-c




Image is for illustration purposes only. Please refer to product description.

Part number	09 16 075 2101
Specification	Han 75DDD F-c
HARTING eCatalogue	https://b2b.harting.com/09160752101

Identification

Category	Inserts
Series	Han [®] DDD

Version

Termination method	Crimp termination
Gender	Female
Size	10 B
Number of contacts	75
PE contact	Yes
Details	PE connection with a Han D [®] crimp contact Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984
----------------	-----------

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors