

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2064600022](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit+ Connector System](#)  
**Description:** Micro-Fit+ Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-24 AWG

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2064600000-TS-000 (PDF)</a>
<a href="#">Product Specification 2064600000-PS-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Packaging Specification 2064600000-PK-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">206460</a>
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<a href="#">Micro-Fit+ Connector System</a>
Product Name	Micro-Fit+
UPC	193264161676

**Physical**

Durability (mating cycles max)	200
Gender	Female
Material - Metal	High Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.066/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm
Wire Size AWG	20, 22, 24
Wire Size mm <sup>2</sup>	0.20-0.50


**Electrical**

Current - Maximum per Contact	12.5A
Voltage - Maximum	600V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2064600000-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2064600000-SD-000
Test Summary	2064600000-TS-000



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[206460 Series](#)

**Use With**

Micro-Fit Receptacle Housing [206461](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool	<a href="#">11030043</a>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 20-30 AWG	<a href="#">638120800</a>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**