

# DEWALT®

**OUTDOOR  
RANGE**

**XR FLEX  
VOLT**

**XR**

[www.DEWALT.com](http://www.DEWALT.com)

**GUARANTEED TOUGH®**



# GUARANTEED TOUGH.

Work smarter with the DEWALT complete outdoor range. The DEWALT XR 18V & 54V outdoor range gives you the power you need, without the inconvenience of cables or using fuel. With the unique XR FLEXVOLT battery system that's compatible with your entire XR range, you have the power to be flexible, quieter, cleaner and of course, to work smarter.

**GUARANTEED TOUGH.®**



## DCMST561 18V XR STRING TRIMMER

DCMST561 is powered by a high-performance DEWALT brushless motor that delivers a runtime of up to 40 minutes on a single 18V 5.0 Ah battery. With a patented split shaft and hinge format, which allows the string trimmer to fold down to a compact size for easy storing or transporting in a vehicle. Engineered to handle the most challenging of tasks, the large 360mm swath and 2mm DEWALT twisted line ensure absolute precision and impressive cutting results.

### DCMST561

Voltage	18 V
Motor	Brushless
Swath	36 cm
Weight	3.5 kg
Runtime (no load)	up to 40 min
Speeds	Variable
Feed system	Bump
Feed reload	Quick load
Line	2 mm twisted








## DCM571 54V FLEXVOLT STRING TRIMMER

Offering all the power of a petrol driven tool without the inconvenience of having to carry / mix fuel. The DCM571 String Trimmer / Brush Cutter also benefits from a 380mm swath as well as brush cutter blade and adapter allowing it to be used for simple grass cutting or heavy duty clearing work.

### DCM571

Voltage	54 V
Charge time	70 min
Cutting width	38 cm
Line cutting speed	0-5100 / 0-5600 rpm
Line length supplied	7.5 m
Weight	6.6kg

## GRASS STRING TRIMMER ACCESSORIES

SKU	DESCRIPTION	FITS
DT20650	 Trimmer Line 2mm x 15.2m	DCM561, DCM571, DCM581
DT20651	 Trimmer Line 2mm x 68.6m	DCM561, DCM571, DCM581
DT20652	 Trimmer Line 2.5mm x 68.6m	DCM571, DCM581
DT20653	 25CM Brushcutter Tri-Blade	DCM571, DCM581
DT20654	 25.5CM Brushcutter Straight Blade	DCM571
DT20655	 23CM Brushcutter 4T Blade	DCM571
DT20656	 Grass Trimmer Replacement Spool & 7.8M 2MM Line	DCM561, DCM571, DCM581
DT20657	 Brushcutter Adapter Set	DCM5712
DT20658	 QUICKFEED Spool - Fits ALL DW Grass Trimmers	DCM561, DCM571, DCM581





**DCM565 18V XR  
BRUSHLESS 30CM CHAINSAW**

The DCM565 18V XR Compact Chainsaw is a versatile tool that can be used in either outdoor or construction applications. Featuring a 300mm bar and chain, the DCM565 is equally effective at cutting logs as it is trimming timber beams in confined spaces. Lightweight and easy to manoeuvre, the DCM565 benefits from a large auxiliary handle, auto-oiling and tool free bar and chain replacement.

**DCM565**

Voltage	18 V
Bar length	300 cm
Lock-off switch	No
Cuts per charge	140
Charge Time	300 min
Weight	3.3 kg



**DCMPS567 18V  
XR POLE SAW**

This ergonomic tool has been meticulously engineered by DEWALT with a lightweight, well-balanced and sturdy form factor, making it easy to manoeuvre even at its fully extended length.



**DCMPS567**

Voltage	18 V
Extended reach	4.5 m
Weight	4.5 kg
Bar length	20 cm
Bucking strips	Yes
Brushless motor	Yes
Cuts per charge	55 (100 x 100 cm)

**DCM575 54V FLEXVOLT  
CHAINSAW**

This high efficiency brushless chainsaw delivers up to 65 cuts per charge. With a 40cm bar and chain this tool provides ultimate performance.

Tool free tensioning/chain replacement and self oiling for smooth, reliable low maintenance cutting.













**DCM575**

Voltage	54 V
Bar length	400 mm
Lock-off switch	Yes
Cuts per charge	130
Charge time	70 min
Weight	5.68 kg



**CHAINSAW ACCESSORIES**

SKU	DESCRIPTION	FITS
DT20660	 Chainsaw 40CM Bar & Chain (DT20663) Pitch: 3/8", Gauge: 0.043", Links: 56, File: 4mm	DCM575
DT20661	 Chainsaw 46CM Bar & Chain (DT20664) Pitch: 3/8", Gauge: 0.050", Links: 62, File: 4mm	DCM585
DT20662	 Chainsaw Oil	All Chainsaws
DT20663	 Replacement 40cm Chain: Pitch: 3/8", Gauge: 0.043", Links: 56, File: 4mm	DCM575
DT20664	 Replacement 46cm Chain: Pitch: 3/8", Gauge: 0.050", Links: 62, File: 4mm	DCM585
DT20665	 30cm Chainsaw Chain & Bar (DT20676) Pitch: 3/8", Gauge: 0.043", Links: 45, File: 4mm	DCM565
DT20676	 Replacement 30cm Chain: Pitch: 3/8", Gauge: 0.043", Links: 45, File: 4mm	DCM565
DT20667	 Chainsaw 20CM Bar & Chain (DT20668) Pitch: 3/8", Gauge: 0.043", Links: 33, File: 4mm	DCMPS567
DT20668	 Replacement 20cm Chain: Pitch: 3/8", Gauge: 0.043", Links: 33, File: 4mm	DCMPS567
DT20666	 Hedge Trimmer Lubricating Spray (300 ML)	All Edge Trimmers






**DCMW564 TWIN 18V XR  
BRUSHLESS LAWN MOWER**

This powerful 36V output brushless cordless lawnmower is equipped with a brushless motor for maximum energy efficiency and extended run times, it has an ergonomic push handle design, 5 height settings and dedicated carry handles for easy transport in between mowing sites or storage.

DCMW564	
Voltage	18+18 V
Cutting width	48 cm
Cutting system	Rotary
No load runtime	22 min
Area of cut	800 m <sup>2</sup>
Grassbox capacity	55 L
Height adjustment	Yes
Cutting heights	25-38-57-74-86 mm
Handle height adjustment	Yes

**DT20671 48CM REPLACEMENT  
BLADE FOR DCMW564**




**DCMPH566 18V XR POLE  
HEDGE TRIMMER**

This pole hedge trimmer has extensive 3.35m reach and innovative articulating 7-position head, combined with an operating speed of 2800spm, professionals can power through demanding jobs in complete control of the tool, whatever the height, shape or density of the foliage. Delivering extreme runtime of up to 75 minutes. With a 550mm blade length and impressive 25mm cutting width, this robust tool provides consistently reliable cutting performance.

DCMPH566	
Voltage	18 V
Max reach	3.35 m
Blade length	55 cm
Blade gap	25 mm
Blade strokes	2800 spm
Runtime (with 5Ah battery)	up to 75 min
Weight	3.6 kg

**DCMHT563 18V XR 25MM HEDGE TRIMMER**


The lightest high-level cordless hedge trimmer available on the market today at just 2.9kg. Compact yet high-performing hedge trimmer reliably delivers up to 75 minutes of runtime. With a blade length of 550mm and a 25mm cut capacity, this rugged hedge trimmer can tackle the toughest of shrubbery, hedging and dense undergrowth, effortlessly slicing through larger branches and stems without experiencing jams.



DCMHT563	
Voltage	18 V
Blade length	55 cm
Blade gap	25 mm
Blade strokes	1400 min
Runtime	up to 75 min
Weight	2.9 kg

**DCM563 18V XR  
HEDGE TRIMMER**

Expand your XR Range with this 18V XR Hedge trimmer that delivers an impressive runtime of up to 75 minutes per charge.



DCM563	
Voltage	18 V
Blade length	55 cm
Blade gap	19 mm
Blade strokes	1400 min
Runtime (with 5ah battery)	up to 75 min
Weight	2.9 kg





**DCMBA572 54V FLEXVOLT AXIAL BLOWER**

Designed for the fast and effective removal of construction debris, workshop waste, leaves, twigs, moss and other stubborn garden matter, this versatile and powerful cordless blower will be welcomed by an array of professional users including construction teams, carpenters, metal and woodworkers, gardeners, landscapers, park clean-up workers and clearance specialists.



**DCMBA572**

Voltage	54 V
Air volume	600 cfm (17 m <sup>3</sup> /min)
Blow speed	200 km/h
Weight	3.8 kg

**DCM572 54V FLEXVOLT HANDHELD BLOWER**

DEWALT has created the XR FLEXVOLT power tool series, enabling construction professionals to use cordless tools for jobs requiring heavy loads that were completely impossible before.


DEWALT XR FLEXVOLT is the only battery in the market that switches from 54V to 18V, making it backwards compatible with your XR power tools.



**DCM572**

Voltage	54 V
Air volume	423 cfm (12 m <sup>3</sup> /min)
Blow speed	207 km/h
Weight	3.2 kg

**BATTERIES AND CHARGERS**

SKU	DESCRIPTION	FITS
DCB184	 18V XR 5Ah LI-ION BATTERY PACK	ALL 18V DEWALT UNITS
DCB546	 54V XR FLEXVOLT 6Ah 18/54V BATTERY PACK	ALL 18V/54V DEWALT UNITS
DCB547	 54V XR FLEXVOLT 9Ah 18/54V BATTERY PACK	ALL 18V/54V DEWALT UNITS
DCB115	 12V/18V XR CHARGER	ALL 18V DEWALT BATTERIES
DCB118	 18V/54V XR FLEXVOLT FAST CHARGER	ALL 18V/54V DEWALT BATTERIES

DeWALT UK  
270 Bath Road, Slough,  
Berkshire. SL1 4DX  
Telephone: 01753 567055

Your DeWALT Dealer:

[www.DEWALT.com](http://www.DEWALT.com)

The yellow and black colour scheme is used on DeWALT Power Tools and Accessories as a trademark.

Be the first to see product news and special offers from DeWALT.  
Register at MYDeWALT to be sent onsite offers by email.  
Simply go to MYDeWALT.DeWALT.co.uk

REGISTER AT

MY **DEWALT**