


USB-C Dock, 4K HDMI, 2x USB-A Ports, Gbe, SD Card Reader, 60W PD Charging

MODEL NUMBER: U442-DOCK11-S



USB-C dock adds HDMI, USB, PD Charging, Ethernet and memory card connectors to your Chromebook, MacBook, smartphone or PC.

Features

USB-C Dock Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport WorkstationThe U442-DOCK11-S expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for connecting to a wired Gigabit Ethernet network, transmitting digital audio and video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device and more—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video SignalsWith a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 4K Video and Digital AudioTo send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the corresponding port to the display using an HDMI cable (sold separately). The HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz. A DVI display may also be connected using an HDMI to DVI adapter (adapters sold separately).

Accesses a Wired Gigabit Ethernet NetworkThe RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Connects Keyboards, Thumb Drives and Other USB PeripheralsThe USB-A hub ports accept up to two USB peripherals, such as flash drives, mice, keyboards and printers. They support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices.

Charges the Connected PD Charging Device or Provides Data Transfer up to 5 GbpsThe USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C dock is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W. It also doubles as a USB-C hub port and supports data transfer rates up to 5 Gbps.

Allows External Memory AccessMemory card slots support Micro SD and SD/MMC cards for transferring data to and from your connected computer, laptop or tablet. Both memory card slots can be used at the same time.

Built-In USB-C Cable Connects in Either DirectionConnect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the PackageThe plug-and-play USB Type-C dock requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. It automatically resumes operation from hibernation and suspend modes. If additional power is required, the 5V DC power jack is compatible with power supplies equipped with a 3.5 x 1.35 x 9.5 millimeter output plug, a positive tip and a negative sleeve.

Highlights

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- 2 USB-A ports transfer data from thumb drives or printers at speeds up to 5 Gbps
- Connects you to a wired Ethernet network when no Wi-Fi is available
- Easy installation with plug-and-play operation—no software required

Applications

- Play video from your laptop or PC on an HDMI display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your notebook or download data from the Ethernet at true 10/100/1000 Mbps Ethernet speeds
- Transfer data to and from a USB flash drive or Micro SD memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements



3-Year Warranty and Environmentally Responsible Design The U442-DOCK11-S comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
 - Display device with DVI* or HDMI input
 - Not for use with Thunderbolt monitors
- *Requires adapter (sold separately)

Package Includes

- U442-DOCK11-S USB-C Docking Station, 4K, HDMI, Thunderbolt 3, USB-A Hub, PD Charging, SD/MicroSD, Gb – 30 Hz, Silver
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213372
OUTPUT	
Charging Ports / Amps	(2) 0.9A; 3A
Charging Watts	60
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	Yes
Product Length (in.)	12
Product Length (cm.)	30.48
Product Length (ft.)	1
Product Length (m.)	0.3
BATTERY	
Battery Charging (1.2 Port)	Yes



USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Power), Green (Link), Yellow (Activity)
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Silver; White
Material of Construction	Aluminium
Shipping Dimensions (hwd / in.)	0.80 x 5.70 x 3.20
Shipping Weight (lbs.)	0.30
Unit Dimensions (hwd / in.)	0.67 x 4.7 x 2.2
Unit Packaging Type	Box
Unit Weight (kg)	0.10
Unit Weight (lbs.)	0.21
ENVIRONMENTAL	
Operating Temperature Range	32 to 131 F (0 to 55 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	5% to 95% RH, Non-Condensing
BTUs	15.7 BTU/Hr
Power Consumption (Watts)	4.6
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB A), Up to 20V 3A (60W) Input (USB C)
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3
CONNECTIONS	
Ports	8
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE); RJ45 (FEMALE)
Side B - Connector 2	(2) USB 3.0 A (FEMALE)
Side B - Connector 3	MICRO SD (FEMALE)
Side B - Connector 4	SD (FEMALE)
Side B - Connector 5	USB Type-C (FEMALE)
Connector Plating	Nickel



FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	HDMI: 3840 X 2160 (4K X 2K) @ 30HZ
HDMI Specification	1.4
HDCP Specification	2.2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5/5e/6 Cables
USB Power Delivery (PD) Charging Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	HDMI; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging
SD Card Specification	SD; Micro SD
USB Power Delivery (PD) Charging Specification	2.0
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>