

USB-C Dual Display Dock, 4K HDMI, VGA, 4K Mini DP, Gbe, 3x USB-A Ports, Audio, SD Card, 60W PD Charging

MODEL NUMBER: U442-DOCK2-S



USB-C docking station adds HDMI, VGA, mDP, USB, PD Charging and other ports to your Chromebook, MacBook, smartphone or PC.

Features

USB-C Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport WorkstationThe U442-DOCK2-S expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting digital audio and video to a large display, adding a thumb drive or other USB peripheral, powering and charging a PD Charging-compliant mobile device, connecting to a Gigabit Ethernet network and a lot more—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Audio/Video SignalsWith a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 4K Video and Digital AudioTo send digital audio and Ultra High Definition video to a 4K-ready HDMI or Mini DisplayPort television, projector or monitor, connect the corresponding port to the display using an HDMI or mDP cable (sold separately). The Mini DisplayPort and HDMI ports support UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz. The VGA port supports high-definition resolutions up to 1920 x 1200, including 1080p, at 60 Hz. Only one display can be connected at a time. A DisplayPort or DVI display may also be connected using an mDP to DP or HDMI to DVI adapter (adapters sold separately).

Connects Keyboards, Thumb Drives and Other USB PeripheralsThe USB-A hub ports accept up to three USB peripherals, such as flash drives, mice, keyboards and printers. They support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices. A BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices.

Charges the Connected Laptop, Smartphone or Other DeviceThe USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U442-DOCK2-S is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W—45W for the USB-C device and 15W dedicated to the U442-DOCK2-S and its USB-A hub ports.

Accesses a Wired Gigabit Ethernet NetworkThe RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Connects Audio EquipmentThe USB-C hub's 3.5 mm mini stereo jack is convenient for connecting speakers, headphones or a microphone to your workstation. You can listen to music or record the latest episode of your podcast.

Allows External Memory AccessThe memory card slots support Micro SD and SD/MMC cards for transferring data to and from your connected computer, laptop or tablet.

Built-In USB-C Cable Connects in Either DirectionConnect the reversible USB-C plug to your source

Highlights

- Transmits audio/video signals from sources supporting USB DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Connects you to a wired Ethernet network when no Wi-Fi is available
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Easy installation with plug-and-play operation—no software required

Applications

- Play video from your laptop or PC on an HDMI, VGA or mDP display, such as an HDTV or projector
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Transfer data to and from a USB flash drive, Micro SD or SD/MMC memory card
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a microphone/headset to record a podcast or listen to music

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports



device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB-C dock requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U442-DOCK2-S comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

USB DisplayPort Alternate

Mode

- Display device with DisplayPort*, Mini DisplayPort, VGA, DVI* or HDMI input
 - Not for use with Thunderbolt monitors
- *Requires adapter (sold separately)

Package Includes

- U442-DOCK2-S USB-C Laptop Docking Station w/HDMI, VGA, GbE, 4K, Thunderbolt 3 - mDP, USB-A, PD Charging, 30 Hz, Silver
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332213488
OUTPUT	
Charging Ports / Amps	0.9A; 1.5A; 3A
Charging Watts	60
INPUT	
Bus Powered	Yes
Product Length (in.)	9.75
Product Length (ft.)	1
BATTERY	
Battery Charging (1.2 Port)	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	



Cable Jacket Rating	VW-1
Color	Silver; White
Material of Construction	PVC, Aluminium
Unit Dimensions (hwd / in.)	0.6 x 4.7 x 4.7
Unit Packaging Type	Box
Unit Weight (kg)	0.23
Unit Weight (lbs.)	0.50
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
BTUs	17.1 BTU/Hr
Power Consumption (Watts)	5
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A Output (USB A), Up to 20V 3A (60W) Input (USB C)
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x
CONNECTIONS	
Ports	11
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE); HDMI (FEMALE); MINI DISPLAYPORT (FEMALE)
Side B - Connector 2	(3) USB 3.0 A (FEMALE)
Side B - Connector 3	MICRO SD (FEMALE); SD (FEMALE)
Side B - Connector 4	RJ45 (FEMALE)
Side B - Connector 5	USB Type-C (FEMALE)
Side B - Connector 6	3.5MM (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	MDP/HDMI: 3840 X 2160 (4K X 2K) @ 30HZ; VGA: 1920 X 1200 (1080P) @ 60HZ
Displayport Specification	1.2
HDMI Specification	1.4



HDCP Specification	1.4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	Stereo Audio
Driver Required	No
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
USB Power Delivery (PD) Charging Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Technology	Cat5/5e; Cat6; DisplayPort; HDMI; Stereo Audio; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); VGA/SVGA; PD Charging
SD Card Specification	SD; Micro SD
USB Power Delivery (PD) Charging Specification	2.0
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>