


USB-C Multiport Adapter, 4K HDMI, 3x USB-A Ports, 100W PD 3.0, HDCP, Gray

MODEL NUMBER: U444-06N-H3U-C



4K USB-C adapter with PD Charging connects a 4K HDMI monitor and 3 USB peripherals to a USB-C or Thunderbolt 3 device.

Features

Mini Docking Station Connects an HDMI Monitor to Your USB-C or Thunderbolt 3 Device This USB-C to HDMI cable helps you transmit digital audio and 4K video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to an HDMI-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen, or streaming video for digital signage in crystal-clear 4K.

Supports USB-C DisplayPort Alternate Mode for Transmitting Audio/Video Signals By connecting the built-in USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers.

Transmits Crystal-Clear 4K HDMI Video and Digital Audio To send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (such as Tripp Lite's P568-Series high-speed HDMI cables, sold separately). The USB to HDMI 4K adapter supports video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz, as well as HDCP 1.4 and HDMI 1.4 compatibility. It's backward compatible with 1080p displays, allowing you to use it with older equipment.

BC 1.2-Compliant USB Port Transfers Data at Fast USB 3.1 Gen 1 Speeds Three USB-A ports accept USB peripherals, such as a flash drive, keyboard and printer, and transfers data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. One port complies with BC 1.2 standards, providing up to 1.5 amps (7.5 watts) for charging and powering mobile devices. The USB Type-C adapter is backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

PD Charging Port Charges Connected Device via AC Wall Charger The USB-C Power Delivery 3.0 port provides power output up to 5 amps (100 watts), which is more than sufficient for charging and powering the connected source device, such as a MacBook or Chromebook.

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 Type-C adapter is specifically designed for the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. About the size of a credit card, the U444-06N-H3U-C fits easily into a pocket, purse or laptop bag for convenient connections on the go.

Highlights

- Transmits video signals from sources supporting USB-C DisplayPort Alt Mode
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Power Delivery port provides 5A (100W) power output for charging connected device
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- 3 USB-A ports support USB 3.1 Gen 1 speeds up to 5 Gbps for fast data transfers

Applications

- Play 4K video from your MacBook or Chromebook on a large-screen HDTV
- Give a video presentation at a meeting, training session or conference
- Write and edit multiple documents on a bigger monitor
- Stream 4K video for digital signage at a trade show
- Charge and power a USB-C or Thunderbolt 3 device
- Connect USB peripherals, such as an external hard drive, printer and hub

System Requirements

- Source device with USB-C or Thunderbolt 3 output that supports USB DisplayPort Alternate Mode



- Display device with HDMI input

Package Includes

- U444-06N-H3U-C USB 3.1 C Adapter with PD Charging, Gray
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332237354
OUTPUT	
Charging Ports / Amps	(1) 1.5A; (1) 5A
INPUT	
Built-In Cable Length (ft.)	0.392
Built-In Cable Length (m)	0.119
Built-In Cable Length (in.)	4.7
Built-In Cable Length (cm)	11.938
Bus Powered	Yes
Product Length (in.)	8.3
Product Length (cm.)	21.08
Product Length (ft.)	0.692
Product Length (m.)	0.211
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Gray
Material of Construction	Aluminum
Unit Dimensions (hwd / in.)	.45 x 1.77 x 3.35
Unit Packaging Type	Box
Unit Weight (kg)	0.09



Unit Weight (lbs.)	0.203
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10% to 85% RH, non-condensing
Storage Humidity Range	5% to 90% RH, non-condensing
Power Provided to Connected Device(s)	USB-C PD Charging = 20V 5A (100W), USB-A BC 1.2 = 5V 1.5A (7.5W)
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB A (FEMALE)
Side B - Connector 4	USB A (FEMALE)
Side B - Connector 5	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	3840 x 2160 @ 30 Hz
HDMI Specification	1.4
HDCP Specification	1.4
USB Hub Ports	Yes
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	Yes
Technology	HDMI; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>