

Product availability : Non-Stock - Not normally stocked in distribution facility



### Main

Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DF22
Product compatibility	DF2FA fuse cartridge DF2FN fuse cartridge
Poles description	1P
Fuse size	22 x 58 mm
Fuse type	, gG , aM
Control type	Toggle
Local signalling	Blown fuse indication
[Ue] rated operational voltage	690 V AC 690 V DC
[Ie] rated operational current	125 A
[Ui] rated insulation voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ipk] rated peak withstand current	19 kA with tubular links IEC 60269-1
Short-circuit withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3 80 kA 690 V IEC 60947-3

### Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1
Product certifications	IEC UL recognized CSA EAC
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical +/- 23°

Connections - terminals	screw clamp terminals 1 0.00...0.05 in <sup>2</sup> (2.5...35 mm <sup>2</sup> )rigid screw clamp terminals 2 0.00...0.04 in <sup>2</sup> (2.5...25 mm <sup>2</sup> )rigid screw clamp terminals 1 0.00...0.05 in <sup>2</sup> (2.5...35 mm <sup>2</sup> )flexible with or without screw clamp terminals 2 0.00...0.04 in <sup>2</sup> (2.5...25 mm <sup>2</sup> )flexible with or without
Tightening torque	35.40 lbf.in (4 N.m)
Height	5.02 in (127.5 mm)
Width	1.38 in (35 mm)
Depth	3.01 in (76.5 mm)
Net weight	0.49 lb(US) (0.221 kg)
Quantity per set	Set of 6

## Environment

Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Ambient air temperature for operation	-4...140 °F (-20...60 °C) with derating above 20°C
IP degree of protection	IP20 IEC 60529
Protective treatment	TH
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility code	DF22

## Ordering and shipping details

Category	21714 - DF FUSEHOLDERS
Discount Schedule	CP1
GTIN	03389118233409
Returnability	No
Country of origin	TN

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------