

Product availability : Non-Stock - Not normally stocked in distribution facility



## Main

Range	TeSys
Device short name	GVAN
Product or component type	Auxiliary contact block
Product compatibility	GV3P GV2RT GV2P GV3L GV2ME GV2L GV2LE
Mounting location	Left side
Pole contact composition	1 NO + 1 NC
Connections - terminals	Control circuit spring terminals 1 0.00...0.00 in <sup>2</sup> (0.75...2.5 mm <sup>2</sup> )flexible without cable end Control circuit spring terminals 2 0.00...0.00 in <sup>2</sup> (0.75...2.5 mm <sup>2</sup> )flexible without cable end

## Complementary

[Ui] rated insulation voltage	600 V UL 508 690 V IEC 60947-1 600 V CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A
Protection type	GB2CB... circuit breaker rating according to operational current for Ue ≤ 415 V GG fuse 10 A
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	300 VA 48 V AC-15 100000 cycles 414 VA 690 V AC-15 100000 cycles 500 VA 110...127 V AC-15 100000 cycles

	500 VA 500 V AC-15 100000 cycles 650 VA 440 V AC-15 100000 cycles 720 VA 230...240 V AC-15 100000 cycles 850 VA 380...415 V AC-15 100000 cycles
Rated operational power in W	120 W 240 V DC-13 100000 cycles 140 W 110 V DC-13 100000 cycles 140 W 24 V DC-13 100000 cycles 180 W 60 V DC-13 100000 cycles 240 W 48 V DC-13 100000 cycles
Height	3.50 in (89 mm)
Width	0.37 in (9.3 mm)
Depth	2.60 in (66 mm)

## Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

## Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901494911
Returnability	No
Country of origin	CZ

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------