



LA1LC020 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

|                           |                   |
|---------------------------|-------------------|
| Range                     | TeSys             |
| Device short name         | LA1LC             |
| Product or component type | Auxiliary contact |

### Complementary

|   |  |
|---|--|
| Range compatibility                         | TeSys Integral contactor breaker   |
| Mounting location                           | Right side   |
| Auxiliary contacts operation                | Instantaneous  |
| Pole contact composition                    | 2 NO + 1 NC contactor state  |
| [Ui] rated insulation voltage               | 690 V  |
| [Ith] conventional free air thermal current | 6 A  |
| Connections - terminals                     | screw clamp terminals 2 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> )<br>screw clamp terminals 1 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) |
| Net weight                                  | 0.22 lb(US) (0.1 kg)   |

### Environment

|                              |                      |
|------------------------------|----------------------|
| Environmental characteristic | Standard environment |
|------------------------------|----------------------|

### Ordering and shipping details

|                   |                                |
|-------------------|--------------------------------|
| Category          | 22384-STARTERS,INTEGRAL,ACCESS |
| Discount Schedule | I11                            |
| GTIN              | 00785901257073                 |
| Returnability     | No                             |
| Country of origin | CZ                             |

### Offer Sustainability

|                        |  |
|------------------------|--|
| REACH Regulation       | <a href="#">REACH Declaration</a>                |
| REACH free of SVHC     | Yes  |
| EU RoHS Directive      | Compliant<br><a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free | Yes  |

|                            |  |
|----------------------------|--|
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|