

## Han F+B cover-agg blue



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 513 5401
Specification	Han F+B cover-agg blue
HARTING eCatalogue	<a href="https://b2b.harting.com/09155135401">https://b2b.harting.com/09155135401</a>

### Identification

Category	Hoods/Housings
Series	Han <sup>®</sup> F+B
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for cable to cable housing With fixing cord

### Version

Locking type	Screw locking
Field of application	Connector for food+beverage industry
Details	<p>Cleaning: For cleaning with high pressure lances, a cleaning distance &gt; 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts.</p> <p>Strain relief: A suitable strain relief is required to enable the F+B connector to resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.</p>

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 in locked position IP6K9K acc. to ISO 20653

### Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤1.12 µm



Pushing Performance

## Material properties

Colour (hood/housing)	Blue
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No
EG1935/2004	compliant

## Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1520
	FDA 21 CFR 177.2600

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors