

# 18000BTU Portable Air Conditioning Unit

Our high performance portable air conditioning features the latest energy saving technology. Fitted with easy-roll casters it can be conveniently moved from room to room as required. A ducted hose is included with the system to vent the exhaust air out of the room. Our Portable air conditioning units benefit from an automatic inbuilt condensate pump (in heat mode), and can evaporate the water out the through the exhaust hose (in cool mode) so generally there is no need to manually empty the water tank (except in extremely humid conditions). These units are also fitted with Voice Control so you can connect this model to your Amazon Alexa or Google Home device.



## Specifications

Model	KYR-55GW/AG
Power Rating (Ph-V-Hz)	1 - 220/240 - 50
Capacity BTU/H (Cooling) kW	18000 / 5.2
Capacity BTU/H (Heating) kW	19000 / 5.6
Power Input (W) Cooling / Heating	2000 / 2043
Current Input (A) Cooling / Heating	8.4 / 8.5
EER (BTU/hr.w)	9.3
COP (W/W)	2.9
Dehumidification (L/h)	1.8
Maximum Noise Output dB(A)	65
Airflow (m3/h)	450
Net Dimension (mm) W/D/H	470 / 370 / 764
Net/Gross Weight (kg)	28 / 30
Room Size	15m sq - 45m sq
Max Conservatory Size (m2)	22.5m sq
Exhaust Hose Length (m)	1.5
Exhaust Hose Diameter (mm)	150
Window Extraction Kit	Yes



**airconditioningcentre®**