

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2070190012](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Family Power Connectors](#)  
**Description:** [Mini-Fit Sigma Sealed Cap for 12 Circuit Plug Housing](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2070180000-PK-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2070170000-TS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 2070170001-TS-000 (PDF)</a>
<a href="#">Product Specification 2070170000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2070170000-AS-000 (PDF)</a>	



**General**

Product Family	Accessories
Series	<a href="#">207019</a>
Component Type	Cap
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Product Name	Mini-Fit Sigma
UPC	193264428595

**Physical**

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Thermoplastic Elastomer
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2070170000-AS-000
Packaging Specification	2070180000-PK-000
Product Specification	2070170000-PS-000
Sales Drawing	2070190000-SD-000
Test Summary	2070170000-TS-000, 2070170001-TS-000

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207019 Series](#)

**Use With**

[Mini-Fit Sigma Sealed Plug Housing](#)  
[2070170012](#)