
PRODUCT-DETAILS

432RS6W

Ind. P&S#432RS6W



General Information

Extended Product Type	432RS6W
Product ID	2CMA167189R1000
EAN	7392696671897
Catalog Description	Ind. P&S#432RS6W
Long Description	Surface socket-outlet, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

Ordering

E-Number (Sweden)	E2416564
E-Number (Finland)	2421217
E-Number (Norway)	1543453
EAN	7392696671897
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	99 mm
Product Net Height	178 mm

Product Net Length	131 mm
Product Net Depth / Length	178 mm
Product Net Weight	0.48 kg

Container Information

Package Level 1 Width	135 mm
Package Level 1 Depth / Length	140 mm
Package Level 1 Height	200 mm
Package Level 1 Gross Weight	0.55 kg
Package Level 1 EAN	7392696671897
Package Level 1 Units	box 1 piece
Package Level 2 Units	174 piece

Technical UL/CSA

Ampere Rating UL/CSA	30 A
Tightening Torque UL/CSA	10.6 in-lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CMC700005D0001
Declaration	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	1613211
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+N+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	2.5 ... 10 mm ²
Cable Diameter	25 mm
Cable Entry Position	Cable entry Ø 25mm
Color	Red
Connection Type	Screw
Degree of Protection	IP67 IP69
Enclosure Material	Thermoplastic polyester (PBT)
Frequency (f)	50 Hz 60 Hz
Function	Surface socket outlet
Housing Material	Thermoplastic (PBT)

Invoice Description	Ind. P&S#432RS6W
Material	Plastic
Mounting Holes	60x148,2
Number of Poles	5
Order Multiple	1 piece
Product Main Type	TRS
Product Name	Wall mounted socket
Protection Type	Watertight
Rated Current (I_n)	32 A
Rated Voltage (U_r)	200/346 ... 240/415 V
Recommended Screw Driver	PH2
RoHS Date	L23
Standards	IEC 60309-1, -2
Suitable For	Surface Socket Outlets
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700002D0001
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440510
UNSPSC	39120000

Technical

Wire Size	12 ... 10 AWG
Tightening Torque	1.2 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Surface Socket Outlets

