

PRODUCT-DETAILS

# M12-C01

## M12-C01 M12-5 female screw connector



### General Information

Extended Product Type	M12-C01
Product ID	2TLA020055R1000
EAN	7350024452297
Catalog Description	M12-C01 M12-5 female screw connector
Long Description	Straight M12-5 female connector with cable screw connection. Cable diameter range 2.5–6.5 mm.

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	8544429090

### Popular Downloads

Data Sheet, Technical Information	2TLC010001C0202
-----------------------------------	-----------------

### Dimensions

Product Net Depth / Length	70 mm
----------------------------	-------

Product Net Height	20 mm
Product Net Width	20 mm
Product Net Weight	0.02 kg

## Technical

Degree of Protection	IP65
Rated Control Supply Voltage (U <sub>s</sub> )	24 V
Suitable For	JSHD4-1-AC Adam DYN-Info M12-5 Adam DYN-Status M12-5 Adam DYN-Reset M12-5 Adam OSSD-Info M12-5 Adam OSSD-Reset M12-5 Adam AS-i M12-4

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE	NoDecNee
--------------------------------	----------

## Classifications

Object Classification Code	X
ETIM 4	EC002638 - Cable connector
ETIM 5	EC002638 - Cable connector
ETIM 6	EC002062 - Sensor-actuator connector
ETIM 7	EC002635 - Circular connector for field assembly (industrial connector)
UNSPSC	39121438
E-Number (Sweden)	3861434

## Categories

Low Voltage Products and Systems → Control Products → Safety Products → Cables and Connectors

Low Voltage Products and Systems → Control Products → Safety Products → Safety Sensors, Switches and Locks Accessories

